



Burrs

Hartmetallfrässtifte / Fraises limes / Fresas rotativas de metal duro

Tree

Spitzbogenform
Ogive
Ojival



	3	3	3	6	6	8	10	12
d1 mm	3	3	3	6	6	8	10	12
l1 mm	6	10	13	13	16	19	19	19
d2 mm	3	3	3	3	6	6	6	6
l2 mm	38	38	38	45	50	65	65	65
s	GT6220	GT6230	GT6200	GT6240	GT6400	-	GT6500	GT6700
d	GT6220D	GT6230D	GT6200D	GT6240D	GT6400D	GT6450D	GT6500D	GT6700D
d-max™	-	-	-	-	-	-	-	-
c	-	-	-	-	GT6400C	-	GT6500C	-
k	-	-	GT6200K	-	GT6400K	GT6450K	GT6500K	-
alu	-	-	-	-	-	-	-	-
I.S.O. Ref.	G030603	G031003	G031303	G061303	G061606	G081006	G101906	G121906
SCTI Nr.	SG-41M	SG-43M	SG-44M	SG-51M	SG-1M	SG-2M	SG-3M	SG-13M
IPC Code	49	49	49	49	25	25	25	25


	12	12	16	16
d1 mm	12	12	16	16
l1 mm	25	25	25	25
d2 mm	6	8	6	8
l2 mm	70	70	70	70
s	GT6800	GT6800-8	GT6900-6	GT6900
d	GT6800D	GT6800D-8	GT6900D-6	GT6900D
d-max™	GTDX680	-	-	-
c	GT6800C	-	-	-
k	GT6800K	-	-	-
alu	-	-	-	-
I.S.O. Ref.	G122506	G122508	G162506	G162508
SCTI Nr.	SG-5M	SG-5M8	SG-6M	SG-6M8
IPC Code	25	25	25	25

Burrs

Hartmetallfrässtifte / Fraises limes / Fresas rotativas de metal duro

RAPIDE® Coated burrs - Tree

RAPIDE® Spitzbogenform
RAPIDE® Ogive
RAPIDE® Ojival



	3	3	3	6	6	8	10	12
d1 mm	3	3	3	6	6	8	10	12
l1 mm	6	10	13	13	16	19	19	19
d2 mm	3	3	3	3	6	6	6	6
l2 mm	38	38	38	45	50	65	65	65
s- RAPIDE®-D	GCZ6220	GCZ6230	GCZ6200	GCZ6240	GCZ6400	-	GCZ6500	GCZ6700
d- RAPIDE®-D	GCZ6220D	GCZ6230D	GCZ6200D	GCZ6240D	GCZ6400D	GCZ6450D	GCZ6500D	GCZ6700D
d-max™ RAPIDE®-D	-	-	-	-	-	-	-	-
c- RAPIDE®-D	-	-	-	-	GCZ6400C	-	GCZ6500C	-
k- RAPIDE®-D	-	-	GCZ6200K	-	GCZ6400K	GCZ6450K	GCZ6500K	-
alu- RAPIDE®-A	-	-	-	-	-	-	-	-
I.S.O. Ref.	G030603	G031003	G031303	G061303	G061606	G081006	G101906	G121906
SCTI Nr.	SG-41M	SG-43M	SG-44M	SG-51M	SG-1M	SG-2M	SG-3M	SG-13M
IPC Code	22	22	22	22	22	22	22	22

	12	12	16	16
d1 mm	12	12	16	16
l1 mm	25	25	25	25
d2 mm	6	8	6	8
l2 mm	70	70	70	70
s- RAPIDE®-D	GCZ6800	GCZ6800-8	GCZ6900-6	GCZ6900
d- RAPIDE®-D	GCZ6800D	GCZ6800D-8	GCZ6900D-6	GCZ6900D
d-max™ RAPIDE®-D	GCZDX680	-	-	-
c- RAPIDE®-D	GCZ6800C	-	-	-
k- RAPIDE®-D	GCZ6800K	-	-	-
alu- RAPIDE®-A	-	-	-	-
I.S.O. Ref.	G122506	G122508	G162506	G162508
SCTI Nr.	SG-5M	SG-5M8	SG-6M	SG-6M8
IPC Code	22	22	22	22

Additional lead times may apply on coated burrs.
Längere Lieferzeiten dürfen mit beschichteten Hartmetallfrässtiften gelten.

Délais de livraison peuvent être plus longs pour les fraises limes revêtues.
Las fresas recubiertas pueden tener un plazo de entrega más largo.