


## 64382 HLX-C 200-15

Halogen lamps, current-controlled with PK30d base



### Areas of application

- Airfield lighting

### Product benefits

- Reduced operation and maintenance costs due to long life time
- Instant and constant light output over the lamp life
- Flicker-free operation
- Mercury-free

### Product features

- Dimmable
- Available with connector combinations A, B, C/Z on request
- Infrared radiation output that provides light in the worst of conditions





## Technical data

### Electrical data

Nominal voltage	30.3 V
Nominal wattage	200.00 W
Nominal current	6.60 A

### Dimensions & weight



Product line drawing

Base

Diameter	13.5 mm
Length with base excl. base pins/connection	36.00 mm
Mounting length	16.0 mm
Light center length (LCL)	20.0 mm
Length	57.0 mm

### Lifespan

Lifespan	1500 h
----------	--------

### Additional product data

Base (standard designation)	PK30d
-----------------------------	-------

### Capabilities

Burning position	s90
------------------	-----

### Country specific categorizations

LIF	J1/84
Order reference	64382 HLX-C 200

## Product datasheet

---

### Country specific information

---

Product code	METEL code	SEG number	STK-Number	UK Org
4008321345752	OSRH64382HLXC	8327808	-	-

---

## Product datasheet

---

### Safety advice

---

To prevent personal injury or damage to property, halogen lamps may only be operated in suitable luminaires designed with suitable mechanisms (protective shields, grids, etc.) to ensure that in the event of a lamp bursting no parts/shards can escape and that during operation no ultraviolet radiation can escape. There must also be a warning sign to indicate that the lamps give off high levels of heat. Detailed information is available on request.

---

### Logistical Data

---

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321345752	64382 HLX-C 200-15	Folding carton box 1	37 mm x 33 mm x 71 mm	0.09 dm <sup>3</sup>	16.00 g
4008321345769	64382 HLX-C 200-15	Shipping carton box 100	191 mm x 154 mm x 341 mm	10.03 dm <sup>3</sup>	2241.00 g

---

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### References / Links

---

For more information on airfield lamps see the brochure:

"The reliable guiding stars - Effective solutions for airfield lighting: Tungsten halogen lamps and LED light sources".

---

### Disclaimer

---

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

---