




A friend for life®

XONIC XM
ESD/EGB

RS varenumre er tilføjet i venstre side.



FOR USE IN ESD-AREA

When working on electronic components, electrostatic discharge may lead to damage or destruction of sensitive semiconductors or other components. Therefore, safety measures for work on electrostatically endangered components are imperative. These dissipative C.K screwdrivers offer additional and outstanding protection against electrostatic discharge in ESD safe areas. XonicXM ESD/EGB Screwdrivers: manufactured and tested according to DIN 91953 as well as to DIN EN 100-015/1.



SLOT 4880X ESD ▲													
ORDER REF												BOX QTY	
	mm	in	mm	in	mm	in	mm	in	mm	in			g
343-2589	T4880XE508	60	2 3/8	0,8	1 3/2	0,20	.008	2,5	3/32	97	3 13/16	10	6
343-2595	T4880XE512	60	2 3/8	1,2	3/64	0,25	.010	2,5	3/32	97	3 13/16	10	6
343-2602	T4880XE515	60	2 3/8	1,5	1/16	0,30	.012	2,5	3/32	97	3 13/16	10	6
343-2618	T4880XE518	60	2 3/8	1,8	5/64	0,30	.012	2,5	3/32	97	3 13/16	10	6
343-2630	T4880XE256	60	2 3/8	2,5	3/32	0,40	.016	2,5	3/32	97	3 13/16	10	6
343-2646	T4880XE257	75	3	2,5	3/32	0,40	.016	2,5	3/32	97	3 13/16	10	6
343-2652	T4880XE310	100	4	3,0	1/8	0,50	.020	3,0	1/8	97	3 13/16	15	6
343-2668	T4880XE315	150	6	3,0	1/8	0,50	.020	3,0	1/8	97	3 13/16	20	6
343-2674	T4880XE324	240	9 1/2	3,0	1/8	0,50	.020	3,0	1/8	97	3 13/16	25	6
343-2680	T4880XE410	100	4	4,0	5/32	0,60	.024	4,0	5/32	97	3 13/16	20	6
343-2696	T4880XE415	150	6	4,0	5/32	0,60	.024	4,0	5/32	97	3 13/16	25	6
343-2703	T4880XE45	250	10	4,5	11/64	0,60	.024	4,5	11/64	97	3 13/16	45	6



PHILLIPS 4882X ESD

ORDER REF	SIZE								BOX QTY	
		mm	in	mm	in	mm	in			
343-2719	T4882X0 ESD	PH 000	60	2 3/8	2,5	3/32	97	3 13/16	10	6
343-2725	T4882X00 ESD	PH 00	60	2 3/8	2,5	3/23	97	3 13/16	10	6
343-2731	T4882X000 ESD	PH 0	60	2 3/8	3,0	1/8	97	3 13/16	15	6
343-2747	T4882X1 ESD	PH 1	80	3 1/8	4,5	11/64	97	3 13/16	25	6
343-2753	T4882X11 ESD	PH 1	185	7 1/4	4,5	11/64	97	3 13/16	40	6
343-2769	T4882X12 ESD	PH 1	285	11 1/4	4,5	11/64	97	3 13/16	50	6



TORX 4877X ESD

ORDER REF	SIZE								BOX QTY	
		mm	in	mm	in	mm	in			
343-2999	T4877XESD04	TX 04	50	2	2,5	3/32	97	3 13/16	10	6
343-3009	T4877XESD05	TX 05	50	2	2,5	32	97	3 13/16	10	6
343-3015	T4877XESD06	TX 06	50	2	3,5	9/64	97	3 13/16	15	6
343-3021	T4877XESD07	TX 07	50	2	3,5	9/64	97	3 13/16	15	6
343-3037	T4877XESD08	TX 08	60	2 3/8	3,5	9/64	97	3 13/16	15	6
343-3043	T4877XESD09	TX 09	60	2 3/8	4,0	5/32	97	3 13/16	15	6
343-3059	T4877XESD10	TX 10	80	3 1/8	4,0	5/32	97	3 13/16	15	6
343-3065	T4877XESD15	TX 11	80	3 1/8	4,0	5/32	97	3 13/16	20	6



TAMPERPROOF TORX 4881X ESD

ORDER REF	SIZE								BOX QTY	
		mm	in	mm	in	mm	in			
343-3087	T4881XESD07	TX 07	50	2	3,5	9/64	97	3 13/16	15	6
343-3093	T4881XESD08	TX 08	60	2 3/8	3,5	9/64	97	3 13/16	15	6
343-3100	T4881XESD09	TX 09	60	2 3/8	4,0	5/32	97	3 13/16	15	6
343-3116	T4881XESD10	TX 10	80	3 1/8	4,0	5/32	97	3 13/16	15	6
343-3122	T4881XESD15	TX 15	80	3 1/8	4,0	5/32	97	3 13/16	20	6



NUT DRIVER 4840X ESD

ORDER REF									BOX QTY	
		mm	in	mm	in	mm	in			g
343-3144	T4840XESD32	60	2 3/8	3,2	4.0	5/32	97	3 13/16	20	3
343-3150	T4840XESD35	60	2 3/8	3,2	4.0	5/32	97	3 13/16	20	3
343-3166	T4840XESD40	60	2 3/8	3,2	4.0	5/32	97	3 13/16	20	3
343-3172	T4840XESD45	60	2 3/8	3,2	4.0	5/32	97	3 13/16	20	3
343-3188	T4840XESD50	60	2 3/8	3,2	4.0	5/32	97	3 13/16	20	3
343-3194	T4840XESD55	60	2 3/8	3,2	4.0	5/32	97	3 13/16	20	3



XONIC ESD SCREWDRIVER SET 4884X ESD

340-1771

Set of 4 Xonic screwdrivers, slotted and phillips.

Contents:

- 4880X ESD 1.5 x 60. 2.5 x 75. 3.0 x 100mm
- 4882X ESD PH 0 x 60mm

DIMENSIONS 316 x 133 x 28mm

WEIGHT 70g

BOX QTY 1

ORDER REF T4884XESD



XONIC ESD SCREWDRIVER SET 4877PX

340-1793

Set of 7 Xonic Torx screwdrivers.

Contents:

- 4877X TX 06, TX 07, TX 08, TX 09, TX 10, TX 15, TX 20

DIMENSIONS 316 x 193 x 28mm

WEIGHT 120g

BOX QTY 1

ORDER REF T4877PX