

Crimping pliers - CRIMPFOX-C50 - 1212340

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Basic pliers, for accommodating dies for a wide range of contact types up to 50 mm²

Why buy this product

- Wide variety of available dies
- A mechanical drive system keeps the level of force required to an absolute minimum
- Easily foldable jaw holders mean that the dies can be changed quickly



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 454865
Weight per Piece (excluding packing)	99.99 g
Custom tariff number	82055980
Country of origin	Germany

Technical data

Dimensions

Length (b)	280 mm
Height	65 mm
Width (a)	60 mm

General

Color	black
Compression	universal

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301

Crimping pliers - CRIMPFOX-C50 - 1212340

Classifications

eCl@ss

eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Accessories

Accessories

Die

Crimping pliers - CRIMPFOX-C50 - 1212340

Accessories

Replacement die - CRIMPFOX-C50 RCI 10/DIE - 1212346



Die (pair), for CRIMPFOX-C50, for insulated ring cable lug 10 mm², oval crimp

Replacement die - CRIMPFOX-C50 RCI 16/DIE - 1212347



Die (pair), for CRIMPFOX-C50, for insulated ring cable lug 16 mm², oval crimp

Replacement die - CRIMPFOX-C50 RCI 25/DIE - 1212348



Die (pair), for CRIMPFOX-C50, for insulated ring cable lug 25 mm², oval crimp

Replacement die - CRIMPFOX-C50 RC 35/M-DIE - 1212343



Die (upper part), for CRIMPFOX-C50, for non-insulated cable lugs (DIN 46234) 6 + 35 mm², indent crimp

Replacement die - CRIMPFOX-C50 RC 25/F-DIE - 1212344



Die (lower part), for CRIMPFOX-C50, for uninsulated cable lugs (DIN 46228) 25 mm², indent crimp

Crimping pliers - CRIMPFOX-C50 - 1212340

Accessories

Replacement die - CRIMPFOX-C50 RC 35/F-DIE - 1212345



Die (lower part), for CRIMPFOX-C50, for uninsulated cable lugs (DIN 46228) 35 mm², indent crimp

Replacement die - CRIMPFOX-C50 RCT 35-1/DIE - 1212341



Die (pair), for CRIMPFOX-C50, for copper tube lug 35 mm², WM crimp

Replacement die - CRIMPFOX-C50 RCT 50-1/DIE - 1212342



Die (pair), for CRIMPFOX-C50, for copper tube lug 50 mm², WM crimp

Replacement die - CRIMPFOX-C50 R25-35/DIE - 1212349



pre-round die (pair), for CRIMPFOX-C50, for sector cable 25 + 35 mm²

Replacement die - CRIMPFOX-C50 R35-50/DIE - 1212350



pre-round die (pair), for CRIMPFOX-C50, for sector cable 35 + 50 mm²

Crimping pliers - CRIMPFOX-C50 - 1212340

Accessories

Replacement die - CRIMPFOX-C50 R50-70/DIE - 1212351



pre-round die (pair), for CRIMPFOX-C50, for sector cable 50 + 70 mm²
