


280 LTSP

Long angled hexagon keys with spherical head - inch-sizes

- For Allen screws
- Model giving a working angle of up to 25° with respect to the axis of the screw
- Special Chrome Vanadium steel
- Burnished finish


"	a mm	L mm	code	
1/16	14	62,5	280091	5
5/64	13,5	75	280092	5
3/32	17,5	84,5	280093	5
1/8	20	90	280094	5
5/32	25	100	280095	5
3/16	27	117	280096	5
7/32	30,5	135,5	280097	5
1/4	33	141,5	280098	5
5/16	36	150	280099	5
3/8	37,5	170,5	280100	5



280 LTS/S9

Set of nine long angled hexagon keys with spherical head

- (280 LTS/1,5÷10 mm)
- Supplied in plastic holder
- Burnished finish


n° gr	code	
350	280084	1



280 LTSP/S9

Set of nine long angled hexagon keys with spherical head - inch sizes

- (280 LTSP/1/16-5/64-3/32-1/8-5/32-3/16-7/32-1/4-3/8")
- Supplied in plastic holder
- Burnished finish

n° gr	code	
320	280089	1


280 LTS/SV9


Empty plastic holder

n° gr	code	
30	280058	1

280 LTSP/SV9

Empty plastic holder

n° gr	code	
30	280088	1





280 D

UNI 10753

Screwdrivers for Allen screws with handgrip

- Ergonomic three-material grip
- Chrome Vanadium steel blade
- Burnished finish


mm	a mm	L mm	code	
1,5	75	169	02800221	5
2	75	169	02800222	5
2,5	75	169	02800223	5
3	75	169	02800224	5
4	100	178	02800226	5
5	100	209	02800228	5
6	100	220	02800230	5




280 TS

Screwdrivers with spherical head and handgrip

- For Allen screws
- Model with spherical head giving a working angle of up to 25° with respect to the axis of the screw
- Ergonomic three-material grip
- Special Chrome Vanadium steel blade
- Burnished finish


mm	a mm	L mm	code	
2	75	220	02800259	5
2,5	75	169	02800260	5
3	75	169	02800261	5
4	75	169	02800263	5
5	100	178	02800265	5
6	100	209	02800267	5



280 H

Angled hexagon keys with handgrip


- For Allen screws
- Ergonomic grip
- Special Chrome Vanadium steel blade
- Chrome plated finish


mm	a mm	L mm	code	
2	90	133	02800302	5
2,5	90	133	02800303	5
3	90	133	02800304	5
3,5	90	133	02800305	5
4	130	183	02800306	5
4,5	130	183	02800307	5
5	130	183	02800308	5
6	175	240	02800310	5
7	175	240	02800311	5
8	175	240	02800312	5
10	175	240	02800314	5

280 H/SE11

Set of eleven hexagon keys with handgrip

- (280 H/2÷10)


n° gr	code	
805	02800317	1



280 HTS

Angled hexagon keys with spherical head and handgrip


- For Allen screws
- Model giving a working angle of up to 25° with respect to the axis of the screw
- Same features of 280 H


mm	a mm	L mm	code	
2,5	90	133	02800321	5
3	90	133	02800322	5
4	130	183	02800324	5
5	130	183	02800326	5
6	175	240	02800327	5
8	175	240	02800329	5
10	175	240	02800331	5

280 HTS/SE7

Set of seven angled hexagon keys with spherical head and handgrip

- (280 HTS/2,5÷10 mm)


n° gr	code	
670	02800337	1



280 HTX

Angled keys with handgrip for TORX® screws

- Ergonomic grip
- Special Chrome Molybdenum steel blade
- Chrome plated finish

n°	a mm	L mm	code	
T6	90	133	02800341	2
T7	90	133	02800342	2
T8	90	133	02800343	2
T9	90	133	02800344	2
T10	90	133	02800345	2
T15	90	133	02800346	2
T20	130	183	02800347	2
T25	130	183	02800348	2
T27	130	183	02800349	2
T30	175	240	02800350	2
T40	175	240	02800351	2
T45	175	240	02800352	2
T50	175	240	02800353	2