

Product data sheet

Specifications



Shaft extension, TeSys GS, length 320mm, cross section 10 x 10 mm, for switches 50-400 A

GS2AE2

Main

Range	TeSys
Device short name	GS2AE
Product or component type	Shaft extension
Accessory / separate part category	Control accessory
Range compatibility	TeSys (TeSys GS) GS2F TeSys (TeSys GS) GS2G TeSys (TeSys GS) GS2J TeSys (TeSys GS) GS2K TeSys (TeSys GS) GS2L TeSys (TeSys GS) GS2M TeSys (TeSys GS) GS2N TeSys (TeSys GS) GS2P TeSys (TeSys GS) GS2Q FuPact (FuPacT GS) GSC50 FuPact (FuPacT GS) GSB63 FuPact (FuPacT GS) GSD63 FuPact (FuPacT GS) GSB100 FuPact (FuPacT GS) GSC125 FuPact (FuPacT GS) GSD125 FuPact (FuPacT GS) GSD160 FuPact (FuPacT GS) GSB200 FuPact (FuPacT GS) GSB250 FuPact (FuPacT GS) GSD250 FuPact (FuPacT GS) GSB400 FuPact (FuPacT GS) GSD400

Switch rated current	50 A 60 A 63 A 100 A 125 A 160 A 200 A 250 A 315 A 400 A
----------------------	---

Complementary

Length	320 mm
Shaft cross section	10 x 10 mm
Net weight	0.28 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2 cm

Package 1 Width	3 cm
Package 1 Length	32.5 cm
Package 1 Weight	253 g
Unit Type of Package 2	P06
Number of Units in Package 2	320
Package 2 Height	77 cm
Package 2 Width	80 cm
Package 2 Length	60 cm
Package 2 Weight	94.788 kg
Unit Type of Package 3	S02
Number of Units in Package 3	20
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	5.393 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------