

## General Information

Extended Product Type:	216MHS6
Product ID:	2CMA167623R1000
EAN:	7392696676236
Catalog Description:	Switched interlocked socket-outlet, 6h, 16A, IP44, 2P+E
Long Description:	Switched Interlocked Socket Outlet, horisontal, earthing sleeve position 6h, rated current 16A, IP44 splashproof, 2-poles+earth, frequency 50-60 Hz, color code Blue

## Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Switched Interlocked Socket Outlets, Horisontal

## Ordering

EAN:	7392696676236
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

## Dimensions

Product Net Width:	168 mm
Product Net Height:	129 mm
Product Net Length:	116 mm
Product Net Depth:	129 mm
Product Net Weight:	0.58 kg

## Container Information

Package Level 1 Width:	144 mm
Package Level 1 Length:	202 mm
Package Level 1 Height:	140 mm
Package Level 1 Gross Weight:	0.66 kg
Package Level 1 EAN:	7392696676236
Package Level 1 Units:	1 piece

## Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1
--------------	---

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

## Additional Information

Additional Information:	Cable entry, knock-outs Ø25mm/M25
Cable Cross-Section:	1.5 ... 4 mm <sup>2</sup>
Cable Entry Position:	Top and bottom
Cable Outlets Per Side:	1xØ25
Color:	Blue
Degree of Protection:	acc. to IEC 60529 IP44
Enclosure Material:	Thermoplastic
Frequency (f):	50 Hz 60 Hz
Function:	Switched interlocked socket outlet, horisontal
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#216MHS6
Mounting Type:	Horisontal
Number of Poles:	3
Object Classification Code:	2CMT005069
Product Main Type:	MHS
Product Name:	Industrial Switched Interlocked Socket Outlet
Protection Type:	Splashproof
Rated Current (I <sub>n</sub> ):	16 A
Rated Voltage (U <sub>r</sub> ):	200 ... 250 V

<b>RoHS Date:</b>	L23
<b>Standards:</b>	IEC 60 309-1, -2, -4
<b>Suitable For:</b>	Switched Interlocked Socket Outlets, Horizontal
<b>Suitable for Product Class:</b>	Industrial Plugs and Sockets

---

### Classifications

---

<b>E-number:</b>	2416812
<b>UNSPSC:</b>	39120000

---

