



Features at a glance

Display	Large 4-line backlit display
Keyboard	ABC
Label customization options	8 font styles 7 font sizes 10 text styles 8 box styles - plus underline
Labels	6 mm, 9 mm, 12 mm, 19 mm
Memory	Last label memory 9-label memory
Power	Lithium-ion battery included Auto-off power saver PC connectivity
Dimensions	L 215 mm x W 111 mm x H 57 mm
Weight (Printer and battery)	500 gr

Available label cassettes for LabelManager™ 420P



Temperature
Resistant



Water
Resistant



UV
Resistant



Easy Peel




LABELS

D1 Standard Labels:
Width: 6, 9, 12 mm Length: 7 m



D1 Flexible Labels for
Curved Surfaces:
Width: 12, 19 mm Length: 3,5 m

Dealer:



High-Performance
Portable Label Maker with
PC or Mac® Connection

DYMO A **NewellRubbermaid** Brand

©2010 DYMO / DYMO bvba, Industriepark-Noord 30 / B-9100 Sint-Niklaas - Belgium
www.dymo.com

S0043620



PC / Mac®



Portable



DYMO
Label™
Software



Multiple
applications



High-performance Portable Label Maker

Connect the LabelManager™ 420P to your PC¹ or Mac^{®2} and use DYMO Label™ Software to design labels on your computer screen, with barcodes, logos or graphics – or to print batches of labels from text in spreadsheet or database files! When disconnected from your computer, the LabelManager™ 420P label maker is a portable labelling powerhouse with an easy to use interface, quick access keys and plenty of fonts and text effects. Plus it runs on a rechargeable lithium-ion battery, so you're always ready to label.

Features

- Use standalone – or connect via USB to your PC or Mac[®] and use DYMO Label™ v.8 Software¹ to print barcodes, logos, batch labels from data files, and much more
- Large 4-line backlit display – shows text effects on screen before you print
- 8 fonts, 7 font sizes, 10 text styles, 8 boxes plus underline
- Quick access keys for entering diacriticals, currency and other symbols
- Powered by a rechargeable lithium-ion battery – no more disposable AA battery expense and inconvenience
- Uses DYMO® D1 labels in 6 mm, 9 mm, 12 mm and 19 mm widths

Package contents

Package includes LabelManager™ 420P label maker, lithium-ion battery pack, charging adaptor, starter D1 label cassette, USB cable, quick start guide and warranty.

www.dymo.com

¹ Windows® XP, Windows Vista®, Windows® 7
² Mac OS® v10.4 or later



Powered by a rechargeable
lithium-ion battery

DYMO Label™ v.8 Software

DYMO Label™ v.8 Software Works with any fonts or graphics on your computer – customise with your company logo and much more!

Multi-application Print labels from within Microsoft® Word, Excel® or Outlook®, Mac® Address Book and CardScan®.

PC or Mac® Works with Windows® XP, Windows Vista®, Windows® 7 or Mac OS® v10.4 or later.



Built for high-productivity
The DYMO® LabelManager™ 420P
is a portable labelling powerhouse.