

LED LENSER® P17R – Rechargeable

The P17R is a large handheld torch, ideal for those that value energy-efficient, rechargeable, and long-lasting LED lighting in tough and demanding working conditions. Its cutting-edge specification includes the latest CREE® Power+ LED light chip, the patented LED Lenser® Advanced Focus System™ for spot to flood beam lighting and Smart Light Technology™ - a clever micro-chip controller that enables a selection of three lighting options (Power, Low Power, and Defence Strobe). There is also a revolutionary new high-efficiency Lithium-ion phosphate rechargeable battery - the Safety Ytrion Cell®. Based on technology previously only found in electric cars it provides faster charging, more charging cycles, very low self-discharge, and a wider temperature operating range. Alongside this new battery power cell, useful functions such as battery life display, residual time display, and charging indicator, are clearly illuminated via a 360° ten-stage power indicator dial. The P17R has true staying power and has been specifically calibrated to deliver exceptionally long burn times. Its full 400 lumen output discharge cycle can be delivered for around 10 hours of use, however, on a low power setting (50 lumens) this masterpiece of engineering will keep shining for nearly two full days (42 hours) without recharge. It features the ingenious Floating Charge System PRO™ which provides a wear-free magnetic contact and easy fuss-free charging (no need to remove the battery for charging). The Ytrion battery can be fully charged in only 2.5 hours. It is supplied with a heavy duty belt clip and charging cradle, packed in a robust yet stylish black gift box.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the-art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Rechargeable large sized hand-held torch optimised for heavy-duty with exceptional run times delivered by a state-of the art Lithium-ion phosphate battery
- Energy efficient CREE® Power+ LED light-chip
- State-of-the-art reliable German engineering
- Advanced Safety Ytrion Cell® battery technology. Superior reliability, faster recharging (only 2.5h) and better sensitivity to temperature variances.
- Advanced Focus System™ Optics. Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Smart Light Technology™. Micro-chip controlled multi-option technology. Three light options (Power, Low, Defence Strobe)
- Emergency Light Function™. Light switched on automatically if power cut.
- Dual function, ten stage battery indicator
- Charging display light
- Speed Focus™ with Fast Lock™. Instant, smooth, stage-less, single-handed beam selection. Position Fast Lock™ to prevent beam accidentally refocusing
- Dynamic Switch™. Instant reactive light selector switch.
- Floating Charge System PRO™. Simple, fuss-free, wear-free contact charging
- Anodised aircraft-grade aluminium casing. Superior robust protection.
- Large head size delivers larger flood or spot beam
- Gold-plated contacts for superior conductivity
- User-friendly two-piece modular design
- Water and dust resistant. IPX54

Technical Information

Size: 300 x 53mm Ø

Power: 400 lumens max

Run Time: up to 42 hours

Beam Distance: up to 420m

Weight: 740grams

Supplied with : : wall/vehicle mount, 360° hands-free belt clip and integrated battery (Ytrion Cell)

Code	Colour	Packaging	Barcode
8417R	Black	Gift Box	4029113841733