







BALL PEIN - WOOD HANDLE

PART NO.	SIZE Wgt (g)	OVERALL L (mm)			G.W. (kg)
92312	454 / 16oz	336	6	20	11.7
92313	680 / 24oz	356	4	20	20.4
92314	910 / 32oz	376	4	20	23.4






CLAW - WOOD HANDLE

PART NO.	SIZE Wgt (g)	OVERALL L (mm)			G.W. (kg)
92322	370 / 13oz	308	6	20	17.0
92323	454 / 16oz	330	6	20	21.0
92324	567 / 20oz	330	6	20	21.0






ENGINEERS - WOOD HANDLE


PART NO.	SIZE Wgt (g)	OVERALL L (mm)			G.W. (kg)
92401	200	285	4	28	5.5
92402	300	300	4	28	8.1
92403	400	320	2	28	7.8
92404	500	320	2	28	9.1
92405	800	350	2	20	5.0
92406	1000	360	2	20	5.6





FINISHING - WOOD HANDLE

PART NO.	A (mm)	OVERALL L (mm)	SIZE Wgt (g)			G.W. (kg)
92501	22	260	160	6	60	6.3
92502	28	300	162	6	36	9.1
92503	35	320	308	6	36	13.6
92504	45	320	454	6	24	13.8
92505	60	385	778	4	16	16.4




 Plastic hammer head is not covered under Lifetime Warranty.



SOFT PLASTIC HAMMER HEAD

PART NO.	OUTSIDE DIAMETER (mm)			G.W. (kg)
92521	22	48	288	8.4
92522	28	48	300	12.4
92523	35	24	300	8.2
92524	45	24	192	18.8
92525	60	24	144	21.0




 Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.



HARD PLASTIC HAMMER HEAD

PART NO.	OUTSIDE DIAMETER (mm)			G.W. (kg)
92531	22	48	288	8.4
92532	28	48	300	12.4
92533	35	24	300	8.2
92534	45	24	192	18.8
92535	60	24	144	21.0




 Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.


DEAD BLOW HAMMER (RUBBER)

PART NO.	A (mm)	OVERALL L (mm)	SIZE Wgt (g)			G.W. (kg)
92901	35	260	400	6	48	18.4
92902	45	286	520	6	36	20.9
92903	55	350	1050	4	24	26.9
92904	65	370	1500	4	16	24.4



- Synthetic rubber of high and impact resistance
- Cast steel of unit material with excellent hardness and impact-absorbing



 Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.