

General Information

Extended Product Type:	DR4/6.EX
Product ID:	1SNA146199R2200
EAN:	3472591461992
Catalog Description:	DR 4/6.Ex Screw Clamp Terminal Blocks - Miniblocks - Grey
Long Description:	DR 4/6.Ex Screw Clamp Terminal Blocks - Feed-through - Grey,4mm ² RatedCrossSection, 6mm Spacing TH 15-5.5 Rail.

Additional Information

ABB Industrial IT Suite:	Control IT
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Ambient Temperature:	-5 ... +40 °C
Color:	Grey
Connection Type:	Screw clamp
Country of Origin:	France (FR)
Customs Tariff Number:	85369010
Data Sheet, Technical Information:	1SNC160004C0204
Declaration of Conformity - CE:	1SND225054U1000
EAC Certificate:	1SND161010A1100
EAN:	3472591461992
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block
Environmental Information:	1SND220001E1002
Flammability According to UL94:	V0
Function:	Feed-through
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNC160004C0204
Insulation Material:	Polyamide
Invoice Description:	DR 4/6.Ex Screw Clamp Terminal Blocks - Miniblocks - Grey
Minimum Order Quantity:	50 piece
Mounting on DIN Rail:	TH15-5.5 (15 x 5.5 mm Mounting Rail) acc. to IEC 60715
Number of Connections:	2
Number of Levels:	1
Object Classification Code:	X
Order Multiple:	50 piece
Package Level 1 EAN:	3472591461992
Package Level 1 Gross Weight:	0.3 kg
Package Level 1 Height:	41 mm
Package Level 1 Length:	150 mm
Package Level 1 Units:	50 piece
Package Level 1 Width:	66 mm
Package Level 2 Gross Weight:	11.15 kg
Package Level 2 Height:	150 mm

Package Level 2 Length:	500 mm
Package Level 2 Units:	1800 piece
Package Level 2 Width:	300 mm
Package Level 3 Units:	86400 piece
Product Main Type:	DR4/6.EX
Product Name:	Terminal Block
Product Net Depth:	26 mm
Product Net Height:	28 mm
Product Net Weight:	6 g
Product Net Width:	6 mm
Product Packing Type:	Box
Rated Cross-Section:	4 mm ²
RoHS Information:	1SND230023F0201
Selling Unit of Measure:	piece
Short Description:	grey Screw Clamp Terminal Blocks DR4/6.EX
Spacing:	6 mm
Sub-Function:	Feed-through
Number of Potentials:	1

