

## ML Candle

ML CANDLE 827 E14 7W SLV

0035303

### Range features



CE

### PRODUCT OVERVIEW

Ordering number	0035303
Technology	Compact Fluorescent
Light colour	827 Homelight
Energy class	A
Average life (Rated) (h)	10000
Lamp shape	Candle
Lamp finish	Frosted
Dimmable	No
Cap/Base	E14
Type	CANDLE
EAN code	5410288353036
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	330
Efficacy (Rated) (lm/w)	47
Watt (Nominal) (W)	7
Equivalent watt (W)	30
Voltage (V)	220-240

# ML Candle

ML CANDLE 827 E14 7W SLV

0035303

## DATA TABLE

### General data

Dry applications use only	Yes
Technology	Compact Fluorescent
Ordering number	0035303
Energy saving lamp	Yes
Average life (Rated) (h)	10000
Energy class	A
Average life (Nominal) (h)	10000
Lamp finish	Frosted
Lamp shape	Candle
Dimmable	No
Cap/Base	E14
Type	CANDLE
EAN code	5410288353036
E-number FI	4940409
E-number SE	8357571
Long description	
Product name	ML CANDLE 827 E14 7W SLV
Lamp mercury content (mg)	<2
Starting time (max) (s)	<1.5
Warm-up time to 60% of full light (max) (s)	<100
Control gear required	NO
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	30000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25

### Optical data

Light colour	827 Homelight
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	330
Lumen maintenance at end of nominal life (%)	60
Luminous flux (Nominal) (lm)	330

## ML Candle

ML CANDLE 827 E14 7W SLV

**0035303**

### Electrical data

<b>kWh per 1000 hours burning time</b>	7
<b>Efficacy (Rated) (lm/w)</b>	47
<b>Watt (Rated) (W)</b>	7
<b>Watt (Nominal) (W)</b>	7
<b>Equivalent watt (W)</b>	30
<b>Voltage (V)</b>	220-240
<b>Lamp power factor</b>	=0.55

### Physical data


<b>Weight (kg)</b>	0.04
<b>Lamp Length (mm) - C/L</b>	113±2
<b>Max. Lamp Diameter (mm) - D</b>	39±1
<b>Single packaging type</b>	Box/Sleeve
<b>Single package dimensions (L x W x H) (cm)</b>	12.00 x 5.00 x 5.00
<b>Outer package dimensions (L x W x H) (cm)</b>	26.00 x 11.00 x 14.00

## ML Candle

ML CANDLE 827 E14 7W SLV

0035303

### TECHNICAL DRAWINGS



### ENERGY LABEL

