

General Information

| | |
|------------------------|--|
| Extended Product Type: | OT200U12 |
| Product ID: | 1SCA022752R1890 |
| EAN: | 6417019244396 |
| Catalog Description: | OT200U12 Non-fusible disconnect switch |
| Long Description: | Handle and shaft must be ordered separately. |

Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors

Ordering

| | |
|-------------------------|---------------|
| EAN: | 6417019244396 |
| Minimum Order Quantity: | 1 piece |
| Customs Tariff Number: | 85365080 |

Dimensions

| | |
|---------------------|----------|
| Product Net Width: | 170 mm |
| Product Net Height: | 170 mm |
| Product Net Depth: | 70 mm |
| Product Net Weight: | 1.577 kg |

Container Information

| | |
|-------------------------------|---------------|
| Package Level 1 Units: | 1 piece |
| Package Level 1 Width: | 183 mm |
| Package Level 1 Height: | 95 mm |
| Package Level 1 Length: | 240 mm |
| Package Level 1 Gross Weight: | 1.577 kg |
| Package Level 1 EAN: | 6417019244396 |

Environmental

| | |
|--------------|---|
| RoHS Status: | Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4 |
|--------------|---|

Additional Information

| | |
|--|---|
| Earthing Switch Type: | No Additional Type |
| Handle Type: | None |
| IIT Publishing Status: | Level 0 - Information enabled |
| Includes: | None |
| Mounting Type: | Normal |
| Number of Poles: | 3 |
| Operating Mechanism: | Mechanism between the poles |
| Operating Mode: | Front Operated |
| Pollution Degree: | 3 |
| Power Loss: | 6.5 W |
| Product Main Type: | OT200U |
| Product Name: | Switch-disconnector |
| Rated Impulse Withstand Voltage (U _{imp}): | 12 kV |
| Rated Insulation Voltage (U _i): | 1000 V |
| Rated Operational Current AC-22A (I _e): | (380 ... 415 V) 250 A (500 V) 250 A (690 V) 250 A |
| Rated Operational Current AC-23A (I _e): | (380 ... 415 V) 250 A (500 V) 250 A (690 V) 250 A |
| Rated Operational Voltage: | 1000 V |
| Rated Short-time Withstand Current (I _{cw}): | for 1 s 8 kiloampere rms |
| Special Functions: | No |
| Standards: | IEC&UL |
| Terminal Type: | Lug terminals |

Certificates and Declarations (Document Number)

| | |
|------------------------------------|-----------------|
| Data Sheet, Technical Information: | 1SCC301020C0201 |
| Declaration of Conformity - CE: | 1SCC301137D0202 |

Classifications

ETIM 5.0: EC000216 - Switch disconnecter

Object Classification Code: Q

