

RhinoPRO 3000™

The Professional Tool for All Your Commercial and Residential Labeling Needs.



The **RhinoPRO 3000** is an easy to use, affordable portable printer with labels specifically developed for high end installations all around your home or job site. It's specifically designed for wire and cable networking, home automation, communication, entertainment, HVAC and security systems.

Features and Benefits:

- "Hot Keys" for easy one-touch labeling application:
 - Flagging for wires and cables
 - Vertical and Horizontal Wraps for wires and cables
 - Fixed length for various locations including security panels, face plates and more
 - DPanel for telephone and data distribution panels
- Powerful text "hot keys" for easy one-touch labeling of over 150 common areas.
- Incremental printing – both numeric and alphabetical
- Large 13 character display is easy to read
- Prints up to 2 lines of text in 5 text sizes and 3 print styles
- Uses 3/8" (9mm) and 1/2" (12mm) RhinoPRO label cassettes
- Battery life indicator alerts you when power is low
- Back-lit display for low-light environments
- User selectable for English, French or Spanish language as well as units of measure (inches or millimeters)
- Requires 6 "AA" batteries (not included)



DYMO®

INDUSTRIAL

**How do you sign
YOUR work?™**

RhinoPRO 3000™

Making Your Installation Look More Professional.

RhinoPRO Labels:

- Thermal transfer print technology is durable, smearproof, and resists chemicals, solvents, grease, heat, moisture and other harsh elements.

- Permanent adhesive results in labels that stick and last in harsh industrial environments.

- Easy-to-peel labels available in split-back and dry-edge varieties.



Easy-peel split-back label

- Powerful text "Hot Keys" give you the ability to choose from over 150 common areas around the home and job site – saving you valuable time. Here's a sample of the many choices...

Location:

Den
Family Room
Master Bedroom
Billiards Room
Garage
Kitchen
Basement

Audio/Video:

CATV
Center Back Speaker
DVD/ VCR
Left Surround Speaker
Subwoofer
S-Video

Security:

Back Door
Camera
CCTV
Driveway
Motion Sensor
Smoke detector

Voice/Data:

Cable Modem
Demarc
Fax
Phone

And, many, many more...

Labeling with "Hot Keys":


- Cable/Wire Wrapping

- Flagging

- Fixed Length labels

- Vertical labels

- And many more...



LABEL SELECTION CHART

Surface Applications	Material*	3/8" (9mm)	1/2" (12mm)	Length Feet (m)
Wire/Cable/Curved/Smooth/Flat/Textured/Highly Textured Surfaces	White Flexible Nylon	n/a	18488	11.5' (3.5m)
Wire/Cable/Curved/Smooth/Flat/Textured/Highly Textured Surfaces	Yellow Flexible Nylon	n/a	18490	11.5' (3.5m)
Smooth/Flat/Textured Surfaces	White Permanent Polyester	18482	18483	18.0' (5.5m)
Smooth/Flat/Textured Surfaces	Metallized Polyester	18485	18486	18.0' (5.5m)

*Black print

Product Specifications:

Part # 15605

Weight: 0.8 lbs (363 grams)

Label Maker Dimensions: 4.5"W x 2.1"D x 7.5"H (114mm x 53mm x 190mm)

Warranty: Limited one year


Includes: RhinoPRO 3000, Impact-Resistant Rubber Bumper, One 1/2" White Flexible Nylon Label Cassette, Instruction Manual, Quick Start Card and Registration Card

Uses 6 "AA" batteries (not included) or optional AC adapter (Part # 15519)

For more information or the name of a DYMO Industrial distributor, please visit www.dymo.com/industrial or call us at **1-800-426-7827**



**How do you sign
YOUR work?™**



USA contact: DYMO Corporation, 44 Commerce Road, Stamford, CT 06902-4561

Canada contact: Esselte Corporation, 333 Foster Crescent, Suite 2, Mississauga, Ontario L5R 3Z9 Canada • 1-800-263-6105

© 2004 DYMO Corporation. DYMO is a registered trademark of Esselte Corporation. RhinoPRO is a trademark of Esselte Corporation.

A1277 10/04