

76PC. 1/4" & 1/2"DR. SOCKET WRENCH SET (METRIC)

PART NO.	CONTENT		G.W.(kg)
09519	76PC.	3	19.4

DESCRIPTION:
 7 - 1/4"Dr. 6pt. Metric Sockets 8, 9, 10, 11, 12, 13, 14mm
 18 - 1/4"Dr. Bit Sockets
 Slotted 4, 5.5, 7mm Phillips #1, #2 Pozidriv #1, #2 Torx® 8, 10, 15, 20, 25, 30, 40 Hex 3, 4, 5, 6mm
 12 - 1/2"Dr. 6pt. Metric Sockets 8, 10, 12, 13, 14, 17, 19, 22, 24, 27, 30, 32mm
 15 - 5/16"Shank 30L Bits
 Slotted 8, 10, 12mm Phillips #3, #4 Pozidriv #3, #4 Torx® 40, 45, 50, 55 Hex 8, 10, 12, 14mm
 2 - 1/2"Dr. Spark Plug Sockets 16, 21mm
 22 - Accessories
 1/4", 1/2"Dr. Quick-Release Ratchets
 1/4"Dr. Sliding T-Bar
 1/4"Dr. Flex Shaft
 1/4"Dr. Wobble Extension Bars 2", 4"
 1/2"Dr. Wobble Extension Bars 5", 10"
 1/4", 1/2"Dr. Universal Joints
 1/4"Dr. Spinner Handle
 1/2"Dr. Sliding T-Bar
 5/16"Shank x 1/2"Dr. Bit Coupler
 Combination Wrenches 8, 10, 11, 12, 13, 14, 17, 19, 22mm



120PC. 1/4" & 3/8" & 1/2"DR. SOCKET WRENCH SET (METRIC & S.A.E.)

PART NO.	CONTENT		G.W.(kg)
09014	120PC.	2	21.0

DESCRIPTION:
 10 - 1/4"Dr. 6pt. Metric Sockets 4, 5, 6, 7, 8, 9, 10, 11, 12, 13mm
 10 - 1/4"Dr. 6pt. S.A.E. Sockets 5/32", 3/16", 7/32", 1/4", 9/32", 5/16", 11/32", 3/8", 7/16", 1/2"
 4 - 1/4"Dr. Metric Deep Sockets 8, 9, 10, 12mm
 7 - 1/4"Shank 25L Tamper-Proof Torx Bits T-10, T-15, T-20, T-25, T27, T-30, T-40
 11 - 3/8"Dr. 6pt. Metric Sockets 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm
 9 - 3/8"Dr. 6pt. S.A.E. Sockets 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8"
 4 - 3/8"Dr. Metric Deep Sockets 13, 14, 15, 17mm
 2 - 3/8"Dr. Spark Plug Sockets 16, 21mm
 17 - 3/8"Dr. Bit Sockets
 Slotted 4, 5.5mm Phillips #1, #2 Pozidriv #1, #2 Torx® 20, 30, 40
 Tamper Proof Torx® 45, 50, 55, 60 Hex 3, 4, 5, 6mm
 8 - 3/8"Dr. E-Torx® Sockets E8, E10, E11, E12, E14, E16, E18, E20
 7 - 1/2"Dr. 6pt. Metric Sockets 20, 21, 22, 24, 27, 30, 32mm
 4 - 1/2"Dr. 6pt. S.A.E. Sockets 5/16", 1", 1-1/16", 1-1/4"
 4 - 1/2"Dr. 6pt. Metric Impact Sockets 17, 19, 21, 23mm
 23 - Accessories
 1/4", 3/8", 1/2"Dr. Quick-Release Ratchets
 1/4"Dr. Spinner Handle
 1/4"Dr. Wobble Extension Bars 2"
 3/8"Dr. Wobble Extension Bars 3", 6"
 1/2"Dr. Wobble Extension Bars 5", 10"
 1/4", 3/8", 1/2"Dr. Universal Joints
 1/4"Shank x 1/4"Dr. Bit Coupler
 Combination Wrenches 8, 9, 10, 11, 12, 13, 14, 17, 18, 19mm



150PC. 1/4" & 3/8" & 1/2"DR. SOCKET WRENCH SET (METRIC & S.A.E.)

PART NO.	CONTENT		G.W.(kg)
09510	150PC.	1	14.0

DESCRIPTION:
 10 - 1/4"Dr. 6pt. Metric Sockets 4, 5, 6, 7, 8, 9, 10, 11, 12, 13mm
 10 - 1/4"Dr. 6pt. S.A.E. Sockets 5/32", 3/16", 7/32", 1/4", 9/32", 5/16", 11/32", 3/8", 7/16", 1/2"
 6 - 1/4"Dr. 6pt. Metric Deep Sockets 4, 5, 6, 7, 8, 9mm
 11 - 3/8"Dr. 6pt. Metric Sockets 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm
 9 - 3/8"Dr. 6pt. S.A.E. Sockets 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8"
 6 - 3/8"Dr. 6pt. Metric Deep Sockets 10, 11, 12, 13, 14, 15mm
 2 - 3/8"Dr. Spark Plug Socket 16, 21mm
 22 - 3/8"DR. Bits Sockets
 Slotted 4, 5.5, 6.5mm Phillips #1, #2, #3 (2pc each)
 Torx® 20, 30, 40 Tamper Proof 45, 50, 55, 60 Hex 3, 4, 5, 6, 8, 10mm
 8 - 3/8"Dr. 6pt. E-Torx® Sockets E8, E10, E11, E12, E14, E16, E18, E20
 4 - 1/2"Dr. 6pt. Metric Impact Sockets 17, 19, 21, 23mm
 7 - 1/2"Dr. 12pt. Metric Sockets 20, 21, 22, 24, 27, 30, 32mm
 4 - 1/2"Dr. 12pt. S.A.E. Sockets 15/16", 1", 1-1/16", 1-1/4"
 6 - 1/2"Dr. 6pt. Metric Deep Sockets 10, 12, 13, 14, 17, 19mm
 45 - Accessories
 1/4", 3/8", 1/2"Dr. Quick-Release Ratchets
 1/4"Dr. Bit Coupler
 1/4"Dr. Spinner Handle
 1/4"Dr. Wobble Extension Bars 4"
 3/8"Dr. Locking Extension Bars 3", 6"
 1/2"Dr. Wobble Extension Bars 5"
 1/2"Dr. Locking Extension Bar 10"
 1/4", 3/8", 1/2"Dr. Universal Joints
 1/4"Shank Torx® Bits (Tamper Proof) T-10, T-15, T-20, T-25, T-27, T-30, T-40
 Hex Key Metric Set (10pcs)
 Combination Wrenches 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm
 Double Box Ratcheting Wrenches 8x10, 12x13, 17x19mm




15PC. 3/4"DR. SOCKET SET (METRIC)

PART NO.	CONTENT		G.W.(kg)
09015	15PC.	1	15.4

DESCRIPTION:
 10 - 12pt. Metric Sockets
 30, 32, 34, 36, 38, 41,
 46, 50, 55, 60mm
 5 - Accessories
 Quick-Release Ratchet
 Sliding T-Bar
 Extension Bars 4", 8"
 Universal Joint



15PC. 3/4"DR. SOCKET SET (S.A.E.) New

PART NO.	CONTENT		G.W.(kg)
09148	15PC.	1	15.4

DESCRIPTION:
 10 - 12pt. Metric Sockets
 1", 1-1/8", 1-1/4", 1-5/16",
 1-3/8", 1-1/2", 1-5/8",
 1-3/4", 1-7/8", 2"
 5 - Accessories
 Quick-Release Ratchet
 Sliding T-Bar
 Extension Bars 4", 8"
 Universal Joint



L-SHAPED TIRE WRENCH New

PART NO.			G.W.(kg)
09531	10	20	24.5

DESCRIPTION:
 13920 - 1/2"Dr. Offset Handle 345mm
 13921 - 1/2"Dr. Dual Head Socket 17x19mm
 13922 - 1/2"Dr. Dual Head Socket 21x23mm

