


115
PIN PUNCH SET 8 pieces

- In metal case with lid
- With movable guide sleeve, -59 with fix guide sleeve
- Driving point made from material 115CrV3, hardened 55 - 59 HRC
- Shank knurled
- Fine grinded and polished



Code	No.	Contents			£
8756780	115	114-09 -14 -18 -24 -28 -34 -39 -59	350	1	

113 - 113 D
DRIFT PUNCH SET 6 pieces


- Chrome-molybdenum-vanadium air hardening steel 45CrMoV7
- Carefully hardened and tempered along the full length
- Striking heads inductively tempered
- Working edge polished and clear varnished



Code	No.	Execution	Contents			£
8753680	113	PVC holder	99 10-1 2 3 99 12-4 5 100-10	460	1	
8754060	113 D	metal case with lid	99 10-1 2 3 99 12-4 5 100-10	755	1	

106 - 106 D
CHISEL AND PUNCH SET 6 pieces


- Chrome-molybdenum-vanadium air hardening steel 45CrMoV7
- Carefully hardened and tempered along the full length
- Striking heads inductively tempered
- Working edge polished and clear varnished



Code	No.	Execution	Contents			£
8725200	106	PVC holder	97-125 150 98-125 99 12-3 100-10 119-4	525	1	
8725710	106 D	Metal case with lid	97-125 150 98-125 99 12-3 100-10 119-4	805	1	

102
CHISEL AND PUNCH SET 6 pieces

- Chrome-molybdenum-vanadium air hardening steel 45CrMoV7
- Carefully hardened and tempered along the full length
- Striking heads inductively tempered
- Working edge polished and clear varnished
- In wooden stand



Code	No.	Contents			£
8723340	102	97-125 150 98-125 99 12-3 100-10 119-4	695	1	

SETS
116 A - 116 L - 119 L
PIN PUNCH SET 6 pieces

- Chrome-molybdenum-vanadium air hardening steel 45CrMoV7
- Carefully hardened and tempered along the full length
- Striking heads inductively tempered
- Working edge polished and clear varnished
- 116 L / 119 L = long pattern


116

116 A

116 L

119 L


Code	No.	Execution	Contents			£
8757240	116	wooden stand	119-3 -4 -5 -6 -7 -8	714	1	
8758050	116 D	metal case with lid	119-3 -4 -5 -6 -7 -8	820	1	
8757670	116 A	PVC holder	119-3 -4 -5 -6 -7 -8	530	1	
8839990	116 L	PVC holder	119-2 -3 -5 -175 -175-4 -175-6	475	1	
8866290	119 L	PVC holder	119-175-4 175-5 175-6 175-7 175-8 175-10	580	1	

