


CTK45NEU

# 1/4" Professional Tools Set - 45 pcs.

The Set includes 45 pieces in high-quality Chrome-Vanadium and SuperLock.  
All pieces are fixed in a handy plastic case with carrying handle.



## SuperLock.

The suit pressure is shifted by new wave profile perfectly on the surfaces of the screwing head and / or the nut / mother, which means approx. 15% higher power transmission. There are no more finish turns of the screwing head or the nut / screw heads, equally damaged nuts / screw heads or hexagonal screws can be loosened problem-free.

| Code No. | Description                      | EAN          |
|----------|----------------------------------|--------------|
| CTK45NEU | Professional Tool Set, 25 pieces | 037103456380 |

## Content CTK45NEU

|    | Sockets, matte, in Chrome-Vanadium and SuperLock quality                                         |
|----|--------------------------------------------------------------------------------------------------|
| 1  | 1/4" Quick Release Ratcheting Drive, 72-tooth, with cushion grip, CrV                            |
| 2  | 1/4" Extension 50 mm and 100 mm, CrV                                                             |
| 1  | 1/4" Universal Joint, CrV                                                                        |
| 13 | 1/4" SuperLock Sockets 4 / 4.5 / 5, / 5.5 / 6 / 7 / 8 / 9 / 10 / 11 / 12 / 13 / 14 mm, CrV, 6 pt |
| 1  | 1/4" Flexible Extension 150 mm, CrV                                                              |
| 2  | 1/4" Phillips® Bit Sockets #1and #2                                                              |
| 2  | 1/4" Pozidriv® Bit Sockets #1and #2                                                              |
| 3  | 1/4" Slotted Bit Sockets: 4 / 5 / 7 mm                                                           |
| 4  | 1/4" Hex Bits Sockets: 3 / 4 / 5 / 6 mm                                                          |
| 6  | 1/4" Torx® Bit Sockets: T8, T10, T15, T20, T25, T30                                              |
| 8  | Hex Key: 1,5 / 2 / 2,5 / 3 / 4 / 5 / 5,5 / 6 mm with Holder                                      |
| 1  | 1/4" Spinner Handle                                                                              |
| 1  | 1/4" Sliding T-Handle, CrV                                                                       |

For further information please contact:

**Apex Tool Group B.V.**

Phileas Foggstraat 16  
7821 AK Emmen  
The Netherlands

Tel.: +31 (0) 591 667500  
Fax: +31 (0) 591 667595  
cs.emmen@apextoolgroup.com



[www.apex-tools.eu](http://www.apex-tools.eu)