


# PRODUCT SPECIFICATION

<b>Brand</b>	C.K
<b>Product Range</b>	Inspection mirrors
<b>Catalogue number</b>	5911, 5912, 5913 & 5914
<b>Date</b>	20/02/2009

<b>Range Description</b> Professional quality inspection mirrors				
<b>Features</b>  <b>All</b> <ul style="list-style-type: none"> <li>Telescopic inspection mirrors with pocket clip (except 5911)</li> <li>Swivel joint heads for convenient adjustment</li> </ul>				
<b>Item Number</b>	<b>Item Description</b>	<b>EAN No</b>	<b>Commodity code</b>	<b>Carton Qty</b>
T5911 20	Inspection Mirror 20mm Dia x 164mm	5013969051162	70099200	6
T5912 38	Inspection Mirror 38mm Dia x 685mm	5013969051179	70099200	6
T5912 55	Inspection Mirror 55mm Dia x 560mm	5013969051186	70099200	6
T5913 32	Inspection Mirror 32mm Dia x 520mm	5013969051193	70099200	6
T5914 55	Inspection Mirror 55mm Dia x 780mm	5013969051216	70099200	6

Technical product information	<b>Telescopic extension range</b>		
	<b>Item</b>	<b>Min</b>	<b>Max</b>
	T5911 20	164	164
	T5912 38	125	685
	T5912 55	125	560
	T5913 32	180	520
	T5914 55	250	780
Standards compliance	None applicable		
User health and safety information	None applicable		
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations		
Material safety data	None applicable		
Warranty	C.K Products are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered		
Country of origin	Taiwan		

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T5911 20	20	15	164	24	40	15	220	30
T5912 38	40	7	185	38	90	10	260	68
T5912 55	60	10	80	56	100	10	280	92
T5913 32	30	10	90	42	65	10	260	62
T5914 55	60	15	335	132	80	20	440	170

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T5911 20	90	250	40	188		
T5912 38	95	270	60	466		
T5912 55	110	280	90	625		
T5913 32	70	260	80	416		
T5914 55	100	450	70	1115		

## Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T5911 20	8	Bag			6	Wallet		
T5912 38	10	Blister	16	Card			58	Box
T5912 55	14	Blister	22	Card			73	Box
T5913 32	10	Blister	12	Card				
T5914 55	14	Blister	24	Card				