

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [34729-0080](#)
Status: **Active**
Overview: [Stac64™ Single, Multi-Pocket and Hybrid Header System](#)
Description: [Stac64™ Receptacle Assembly, 8 Circuits, Polarization A, Black, Tray](#)

Documents:

| | |
|--|--|
| 3D Model | Application Specification AS-34729-020 (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-34729-020 (PDF) | Product Literature (PDF) |

General


| | |
|-----------------------------|---|
| Product Family | PCB Receptacles |
| Series | 34729 |
| Application | Signal, Wire-to-Board |
| Comments | Polarization A |
| Overview | Stac64™ Single, Multi-Pocket and Hybrid Header System |
| Product Literature Order No | 987650-4561 |
| Product Name | Stac64™ |
| UPC | 884982007048 |

Physical

| | |
|--------------------------------|--------------------------------|
| Circuits (Loaded) | 8 |
| Circuits (maximum) | 8 |
| Color - Resin | Black |
| Durability (mating cycles max) | 10 |
| Glow-Wire Compliant | No |
| Guide to Mating Part | No |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | High Temperature Thermoplastic |
| Net Weight | 4.190/g |
| Number of Rows | 2 |
| Orientation | Vertical |
| PC Tail Length | 3.33mm |
| PCB Locator | Yes |
| PCB Retention | None |
| PCB Thickness - Recommended | 1.60mm |
| Packaging Type | Tray |
| Pitch - Mating Interface | 2.54mm |
| Pitch - Termination Interface | 2.54mm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Robotic Placement | None |
| Stackable | Yes |
| Surface Mount Compatible (SMC) | No |
| Temperature Range - Operating | -40°C to +100°C |
| Termination Interface: Style | Through Hole |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 10A |
| Voltage - Maximum | 500V |



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[34729Series](#)

Mates With

[34690](#) , [34691](#) 2.54mm Pitch Stac64™ Vertical Header

Use With

[34803](#) CTX64 Female Terminal

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|--------------|
| Application Specification | AS-34729-020 |
| Product Specification | PS-34729-020 |
| Sales Drawing | SD-34729-020 |

This document was generated on 02/11/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION