







Panel cutting





Connector pitches on panel = 35 mm
Receptacle mating face according to
IEC 61076-3-106 - variant 04
A, B, C jack references according to
IEC 60603-7

Screwing by x4 M3 screws with torque 0,5 N.m
with flat washer under the screw





				Dat.	Name			
33812	23/oct/06	JFB	Detail.	19/dec/05	JFB	 All Dim. in mm Orig. Size DIN A 3	Push-pull RJ Industrial Easy install IP 67 receptacle for other jacks	Maßstab/ Scale 1,5:1
33468	27/April/06	JFB	Insp.					
33447	24/march/06	JFB	Stand.					
33405	20/dec/05	BD	HARTING EURL F-95972 Paris				TB 09 45 545 0030	Blatt/ Page 1
33289	19/dec/05	BD						
Mod.	Dat.	Name					Sub.	






Connector pitches on panel = 35 mm
Receptacle mating face according to IEC 61076-3-106 - variant 04
Jack B reference according to IEC 60603-7
Position dimensions for Harting SMD jack P/N 09 45 551 1100
PCB Layout see TB 09 45 551 1100

Screwing by x4 M3 screws with torque 0,5 N.m with flat washer under the screw



				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	Push-Pull RJ industrial Easy install IP 67 receptacle With position dimensions of Harting SMD jack P/N 09 45 551 1100	Maßstab/ Scale 1,5/1
			Detail.	10/05/06	JFB			
			Insp.					
			Stand.					
33812	23/oct/06	JFB	HARTING EURL F-95972 Paris				TB 09 45 545 0030	Blatt/ Page 2
33468	10/may/06	JFB						
Mod.	Dat.	Name					Sub.	




Connector pitches on panel = 35 mm
Receptacle mating face according to
IEC 61076-3-106 - variant 04

Jack B Ref according to IEC 60603-7

Position dimensions for
Harting right angle jack.
PCB layout see TB 0945 551 1102.
Screwing by x4 M3 screws with torque 0,5 N.m
with flat washer under the screw

Panel thickness 0.8 to 10 mm



				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	Push-Pull RJ industrial Easy install IP 67 receptacle With position dimensions of Harting right angle jack P/N 09 45 551 1102	Maßstab/ Scale 1,5/1	
			Detail.	21/04/06	JFB				
			Insp.						
			Stand.						
33812	23/oct/06	JFB	HARTING EURL F-95972 Paris					TB 09 45 545 0030	Blatt/ Page 3 /
33468	27/apr/06	JFB							
Mod.	Dat.	Name							



Screwing by x4 M3 screws with torque 0,5 N.m
with flat washer under the screw

