


XTL™ Labels



Laminated Wire/Cable Wrap Sheet Labels

- Pre-sized wire/cable wraps with laminated overwrap protect printed areas from oil, chemicals, moisture, abrasion and fading
- Laminated wire/cable wraps protect text against smearing
- In sheet label formats for high-volume installations
- Get the job done fast – print up to five sheets at one time*
- Simply take them with you, peel and apply
- RoHS Compliant

*Results may vary based on printer



Quick Specs

Label Widths	24 mm, 41 mm, 54 mm
Tape Platform	XTL
Printer Compatibility	Laser Printer
Printing System	Thermal Transfer
Temperature Rating	-40°C to 80°C
UL Recognized	Component to UL 969
Country of Origin	Belgium
Material	Polyester

Item Number	Width (mm)	Length (mm)	Labels/ Pack		Length (mm)	Width (mm)	Height (mm)	Weight (kg)	QTY	EAN
1908552	24	23	2592	Unit	325	255	7	0.26	1	071701002730
				Shelf	273	334	30	0.90	3	30071701002731
				Case	339	265	265	7.74	24	50071701002735
				Pallet	1200	800	1210	272.68	32	-
1908553	24	42	2544	Unit	325	255	10	0.47	1	071701002747
				Shelf	273	334	30	1.06	2	30071701002748
				Case	339	265	265	9.02	16	50071701002742
				Pallet	1200	800	1210	313.64	32	-
1908554	24	103	1008	Unit	325	255	13	0.7	1	071701002754
				Shelf	273	334	30	1.52	2	30071701002755
				Case	339	265	265	12.7	16	50071701002759
				Pallet	1200	800	1210	431.4	32	-

DISTRIBUTED BY:
Newell Europe Sàrl
Chemin de Blandonnet 10
1214 Vernier – Switzerland
WWW.DYMO.COM



A **Newell Rubbermaid** Brand
©2015 Newell Europe LLC

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.

XTL™ Labels



Item Number	Width (mm)	Length (mm)	Total count		Length (mm)	Width (mm)	Height (mm)	Weight (kg)	QTY	EAN
1908555	41	23	2040	Unit	325	255	9	0.4	1	071701002761
				Shelf	273	334	30	0.92	2	30071701002762
				Case	339	265	265	7.9	16	50071701002766
				Pallet	1200	800	1210	277.8	32	-
1908556	41	42	1020	Unit	325	255	7.5	0.3	1	071701002778
				Shelf	273	334	30	1.02	3	30071701002779
				Case	339	265	265	8.7	24	50071701002773
				Pallet	1200	800	1210	303.4	32	-
1908557	54	23	1008	Unit	325	255	7	0.27	1	071701002785
				Shelf	273	334	30	0.93	3	30071701002786
				Case	339	265	265	7.98	24	50071701002780
				Pallet	1200	800	1210	280.36	32	-
1908558	54	42	1008	Unit	325	255	11	0.5	1	071701002792
				Shelf	273	334	30	1.12	2	30071701002793
				Case	339	265	265	9.5	16	50071701002797
				Pallet	1200	800	1210	329	32	-

DISTRIBUTED BY:
 Newell Europe Sàrl
 Chemin de Blandonnet 10
 1214 Vernier – Switzerland
 WWW.DYMO.COM

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.



A *Newell Rubbermaid* Brand
 ©2015 Newell Europe LLC