

Sensor/Actuator cable - SAC-6P-100,0-PVC/0,25 - 1550685

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable ring, PVC, black, 6-pos., conductor colors: Brown / white / blue / black /gray / pink, cable length: 100 m



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 170499
Weight per Piece (excluding packing)	4179.0 g
Custom tariff number	85444995
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length of cable	100 m
-----------------	-------

General

Number of positions	6
---------------------	---

Cable

Cable type	PVC black
Cable type (abbreviation)	PVC
Cable abbreviation	LiYY
Conductor cross section	6x 0.25 mm ² (signal line)
AWG signal line	24
Conductor structure signal line	32x 0.10 mm
Core diameter including insulation	1.19 mm ±0.02 mm
Thickness, insulation	≥ 0.23 mm (Core insulation)
Wire colors	brown, white, green, yellow, gray, pink
Overall twist	Six cores around the filler to the core
External sheath, color	Black RAL 9005

Sensor/Actuator cable - SAC-6P-100,0-PVC/0,25 - 1550685

Technical data

Cable

External cable diameter	5.00 mm
Cable weight	41 kg/km
Outer sheath, material	PVC
Material conductor insulation	PVC
Conductor material	Bare Cu litz wires
Insulation resistance	≥ 1 GΩ*km
Conductor resistance	≤ 78 Ω/km
Nominal voltage, cable	300 V
Test voltage, cable	3000 V
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (cable, flexible installation)

Classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27062011

ETIM

ETIM 3.0	EC001855
ETIM 4.0	EC001855
ETIM 5.0	EC001855

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

Approvals

Approvals

Approvals

EAC

Sensor/Actuator cable - SAC-6P-100,0-PVC/0,25 - 1550685

Approvals

Ex Approvals

Approvals submitted

Approval details

EAC

Accessories

Accessories

Stripping tool

Stripping tool - WIREFOX SAC - 1212623



Stripping pliers, for halogen-free sensor/actuator cables (SAC cables), with PUR and PVC insulation, from Ø of 4.4 to 7 mm, any stripping length