




BIT SETS 6.3 MM (1/4")

620-024

BIT SET 1/4" 24 pieces

- ▶ In plastic case
- ▶ Dimensions: 110 x 65 x 31 mm
- ▶ TORX® = reg. trademark of Acument Intellectual Properties, LLC. USA



Sockets

- 680 4 6,5
- 685 3 4 5 6
- 685 X 5 6 8
- 690 1 2
- 690 PZD 1 2 3
- 687TX 8 T9 T10 T15 T20 T25 T27 T30 T40

Accessories

0.185

Code
1815695

No.
620-024

ACCESSORIES FOR BITS 6.3 MM (1/4")

KB 619 - KB 636

ADAPTOR PIECES

for screwdriver bits 1/4"

- ▶ Acc. to DIN 7427 Form A
- ▶ Hex recess drive as per DIN 3126 - D 6.3 (1/4") and square drive Form G as per DIN 3121
- ▶ For hand-operated or power tools
- ▶ For use in power tools, we recommend the use of a locking ring and pin
- ▶ Manganese-phosphated
- ▶ * Length not standardised



○"	○	□"	□	* L	⚖	Code	No.
1/4	6.3	1/2	12.5	35	0.072	6524150	KB 619
1/4	6.3	1/4	6.3	25	0.017	6524230	KB 620
1/4	6.3	3/8	10.0	*	0.040	6530040	KB 630

620 - 630

BIT ADAPTOR 1/4"

- ▶ Hex recess drive as per DIN 3126 - D 6.3 (1/4") and square drive as per DIN 3120 - C 6.3 (1/4") / C 10 (3/8")



○"	○	□"	□	↳ mm ↳	⚖	Code	No.
1/4	6.3	1/4	6.3	25	0.020	1649329	620
1/4	6.3	3/8	10.0	25	0.025	1973312	630

635

PICKUP TOOL FOR BITS

- ▶ Practical pickup tool for easy bit changing without damaging the profiles
- ▶ Suitable for 4 mm, 6.3 mm (1/4") and 8 mm (5/16") bits
- ▶ Protects hands and bit profiles
- ▶ No more slipping with oily or damp fingers, even with bits deeply recessed in the bit holder




⚖ Code No.

670

BIT SCREWDRIVER 1/4"

- ▶ Hex recess drive as per DIN 3126 - D 6.3 (1/4"), for bits
- ▶ Magnetic screw retainer
- ▶ GEDORE vanadium steel



○"	○	L ₁	L ₂	⚖	Code	No.
1/4	6.3	210	100	0.140	6536590	670

670 K

BIT SCREWDRIVER 1/4"

short pattern

- ▶ Hex recess drive as per DIN 3126 - D 6.3 (1/4"), for bits
- ▶ Magnetic screw retainer
- ▶ GEDORE vanadium steel



○"	○	↳ mm ↳	⚖	Code	No.
1/4	6.3	80	0.100	1953796	670 K

1500 ESD-20 BIT

107

