

WE'RE TALKING BUSINESS

With today's mobile communications you routinely contact your customers, suppliers and partners wherever they are. But what about your employees? Can you reach them all easily and economically on site?

With the Motorola CLS446 two-way radios, every employee can be in touch and be ready to respond to a request for help or information at the touch of a button.

There are no call charges, connection costs or contracts to worry about – just one initial purchase that will soon repay itself by delivering a host of business productivity benefits.

TALK ABOUT SUCCESS

Get everyone talking and your business efficiency will soar, especially if you are in a customer-facing environment where good service is a priority.

RETAIL

Using the CLS446 two-way radio your cashiers can get instant price checks. Customer service personnel can talk immediately to warehouse staff for stock checks and delivery updates while management can monitor and join the call at their discretion.

RESTAURANTS

If waiting staff can call managers when tables are ready, you'll seat more customers faster. Similarly, kitchen staff can alert waiting staff when orders are ready.

HOTELS

Check in, make up rooms... The fast pace of today's hotels means that limited staff numbers need to be in constant contact with each other to ensure staff can respond more quickly to guests' requests.

EVENTS

Get organisers, PR and hospitality, security, coach drivers and catering staff talking to one another, and it's much easier to ensure your important day is a success.

BUILT FOR BUSINESS

The CLS446 two-way radio's design and functionality is ideally suited for busy customer-facing teams in the workplace:

Compact design

At just 153 grams the CLS446 will not weigh you down and it's small design means it can be worn both discreetly and comfortably using the included swivel belt holster.

Long battery life

The rechargeable Lithium Ion battery delivers up to 12* hours talk time to cover most shifts. For longer operations you can drop in 3 standard AAA Alkaline batteries when using the battery tray adaptor.

Simple to use

The combination of a rotary on/off/volume switch, battery strength indicator, large push-to-talk button and easy-to-read liquid crystal display makes the CLS446 the ideal communications device to keep your work teams connected.

Cost-free operation

There are no monthly fees, connection charges, line rentals or contracts. Simply charge the battery and you have cost free voice communication.

Clear communication

Avoid congestion with the choice of 8 channels and 121 codes. This helps deliver a crisp, interference-free signal. And never miss a call when using the supplied lightweight headset with boom microphone and push-to-talk switch.

Coverage

With a range of up to 5 km/3 miles** there's ample power to cover most single site hotels, restaurants and shops.

Call or silent contact

Choose from three call tones or select VibraCall™ alert to receive calls discreetly.

* Typical 5% transmit, 5% receive and 90% standby
** Depending on terrain and conditions

NEED AN ANSWER FAST?



JUST PUSH A BUTTON AND ASK...

SIMPLE, COMPACT AND STYLISH DESIGN



COMMUNICATIONS TO IMPROVE CUSTOMER SATISFACTION

MAKE IT THE PERFECT FIT FOR YOUR BUSINESS NEEDS WITH A MOTOROLA ORIGINAL ACCESSORY

With headsets for hands-free operation, and a choice of different power and carrying options, you can tailor CLS446 radios to your exact needs and do even more.



MOTOROLA MEANS BUSINESS

Motorola is a global leader in communications and electronics solutions with 75 years of engineering experience and innovation. The name Motorola is your assurance that you have invested in a product of advanced technology, designed and built to the highest quality.

FEATURES

- 500 mW of power
- 8 Channels
- 121 interference eliminator codes (83 digital and 38 analogue)
- Voice Scrambling
- VOX with lightweight headset (included)
- Keypad lock
- Call tones plus VibraCall™ Alert
- Up to 12 hours battery life
- Backlit LCD
- Battery level meter
- Cloning capabilities (with multi unit charger) allowing you to transfer settings from one radio to another
- AAA battery compatibility (with optional battery tray)
- Dual pin accessory connection
- 1 year replacement warranty



CLS446 business two-way radio
Drop-in radio and battery charger
Rechargeable Lithium Ion Battery
Swivel belt holster
Light-weight headset for hands-free use

CLS 446



MOTOROLA and the Stylized M Logo are registered in the U.S. Patent and Trademark Office. All other product or service names are the property of their respective owners.
© Motorola, Inc. 2004.

CLS.DL/UK/02/04



IT'S TALKING SENSE



CLS 446

BUSINESS TWO-WAY RADIOS

NO LICENCE FEE, AIRTIME CHARGES OR CONTRACTS