

PP 60 pro



- Programming package for easily programming of switching times at your PC or via your smartphone (android from version 2.3)
- Simple and logical
- PC-software and Android-App allows data download from key to PC and/or to your smartphone, modification of data and upload to data-key DK *pro*
- Switching programs can be archived to your PC or smartphone (android)

Smartphone-compatibility PP 60 pro

- Android 2.3.x Gingerbread

Windows-compatibility PP 60 pro

- WIN 2000 (Service Pack 4)
- WIN XP
- WIN VISTA
- WIN 7
- WIN 8

Further information / Accessory

How can you save a switching program? How can you copy a switching program from one time switch to the other? Questions with an easy answer: DK *pro*! The Data-key of the pro-generation provides even more comfort.

Accessory: Data-key DK *pro*

(not included in delivery of the time switch)



Adapted to:

PP 60 *pro* is adapted to all time switches of the *pro*-generation (except: SC 18.10 *pro* / paladin 170 410 *pro* / paladin 173 110 *pro* / 173 113 *pro* / SC 24.10 *pro*)

Software Updates

The Save 'n carry *pro* programming software is subject to constant improvement. Suggestions and requests of our customers are continuously incorporated in updates and new releases of our software.

Highlights


The "always doing programming adapter". Thanks to battery power, Bluetooth technology and the hugomüller Android application PP 60.00 *pro* (Google play) it is the perfect companion for your pocket.

Save 'n carry *pro*

The Save 'n carry Programming package PP 60 *pro* can be together with the data-key DK *pro* a reasonable add-on for your time switches. Program your time switches easily at your PC or at your smartphone and save the switching program via PP 60 *pro* adapter (via USB or bluetooth) on the datakey DK *pro*.

Programming package Save 'n carry PP 60 pro Desktop

Technical data



Power Supply	Battery and/or USB interface
Connectivity	Bluetooth (smartphone) / USB (PC)
Output	1 socket for data-key DK <i>pro</i> and time switch SC 08 <i>pro</i>
Permitted ambient temperature	+5°...+35°C
Storage temperature	-5°...+45°C
Enclosure	POM; PC
Type of protection	IP 00
Contents	Adapter, USB cable
Accessory	Data-key DK <i>pro</i>

Programming via Smartphone



Programming via PC

Bemerkung	Kanal A	Kanal B	Kanal C	Kanal D	Programmtyp	Schaltfunktion	Ein/Aus	Schaltzeit	Startdatum	Stopdatum	Täglich	Mo
Phase 1	x	x	x	x	Standard	Ein/Aus	Ein	07:00			x	Mo
Phase 2	x	x	x	x	Standard	Ein/Aus	Aus	09:00			x	Mo
Phase 3	x	x	x	x	Standard	Ein/Aus	Ein	11:00			x	Mo
Phase 4	x	x	x	x	Standard	Ein/Aus	Aus	13:00			x	Mo
Phase 5	x	x	x	x	Standard	Ein/Aus						
Phase 6	x	x	x	x	Standard	Ein/Aus						
Phase 7	x	x	x	x	Standard	Ein/Aus						
Phase 8	x	x	x	x	Standard	Ein/Aus						
Phase 9	x	x	x	x	Standard	Ein/Aus						

Order number	Description	Delivery contents
PP 60 pro	Programming package	Adapter, USB cable, software on CD
DK pro	Data-key	Data-key

✓ Housing colour