

General Information

| | |
|------------------------|--|
| Extended Product Type: | 463MM6 |
| Product ID: | 2CMA168042R1000 |
| EAN: | 7392696680424 |
| Catalog Description: | Switched interlocked socket-outlet, 6h, 63A, IP44, 3P+N+E |
| Long Description: | Switched Interlocked Socket Outlet, metal, earthing sleeve position 6h, rated current 63A, IP44 splashproof, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red |

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Switched Interlocked Socket Outlets in Metal

Ordering

| | |
|-------------------------|---------------------|
| EAN: | 7392696680424 |
| Minimum Order Quantity: | 1 piece |
| Country of Origin: | Czech Republic (CZ) |

Dimensions

| | |
|---------------------|---------|
| Product Net Width: | 165 mm |
| Product Net Height: | 228 mm |
| Product Net Length: | 183 mm |
| Product Net Depth: | 228 mm |
| Product Net Weight: | 2.65 kg |

Container Information

| | |
|-------------------------------|---------------|
| Package Level 1 Width: | 170 mm |
| Package Level 1 Length: | 300 mm |
| Package Level 1 Height: | 185 mm |
| Package Level 1 Gross Weight: | 2.8 kg |
| Package Level 1 EAN: | 7392696680424 |
| Package Level 1 Units: | 1 piece |

Environmental

| | |
|--------------|---|
| RoHS Status: | Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1 |
|--------------|---|

Certificates and Declarations (Document Number)

| | |
|---------------------------------|-----------------|
| Declaration of Conformity - CE: | 2CMC700005D0001 |
| Environmental Information: | 2CMC700001D0002 |
| RoHS Information: | 2CMC700057D0001 |

Additional Information

| | |
|----------------------------------|---|
| Additional Information: | Cable entry, 4xM40 |
| Cable Cross-Section: | 6 ... 25 mm ² |
| Cable Entry Position: | Top and bottom |
| Cable Outlets Per Side: | 4xM40 |
| Color: | Red |
| Degree of Protection: | IP44 |
| Enclosure Material: | Aluminium |
| Frequency (f): | 50 Hz 60 Hz |
| Function: | Switched Interlocked Socket Outlet, metal |
| IIT Publishing Status: | Level 0 - Information enabled |
| Invoice Description: | Ind. P&S#463MM6 |
| Number of Poles: | 5 |
| Object Classification Code: | 2CMT005069 |
| Product Main Type: | MM |
| Product Name: | Industrial Switched Interlocked Socket Outlet |
| Protection Type: | Splashproof |
| Rated Current (I _n): | 63 A |
| Rated Voltage (U _r): | 346 ... 415 V |
| RoHS Date: | L23 |

| | |
|------------------------------------|--|
| Standards: | IEC 60 309-1, -2, -4 |
| Suitable For: | Switched Interlocked Socket Outlets in Metal |
| Suitable for Product Class: | Industrial Plugs and Sockets |

Classifications

| | |
|------------------|----------|
| E-number: | 2417112 |
| UNSPSC: | 39120000 |

