

### General Information

Extended Product Type:	416RAU6W
Product ID:	2CMA167030R1000
EAN:	7392696670302
Catalog Description:	Socket-outlet, panel mounting, 6h, 16A, IP67, unified flange, angled, 3P+N+E
Long Description:	Socket-outlet, panel mounting, earthing sleeve position 6h, rated current 16A, IP67 watertight, unified flange, angled, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

### Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Socket Outlets for Panel Mounting

### Ordering

EAN:	7392696670302
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

### Dimensions

Product Net Width:	104 mm
Product Net Height:	104 mm
Product Net Length:	99 mm
Product Net Depth:	104 mm
Product Net Weight:	0.18 kg

### Container Information

Package Level 1 Width:	112 mm
Package Level 1 Length:	114 mm
Package Level 1 Height:	115 mm
Package Level 1 Gross Weight:	0.18 kg
Package Level 1 EAN:	7392696670302
Package Level 1 Units:	1 piece

### Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

### Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

### Additional Information

Additional Information:	IP69
Cable Cross-Section:	1.5 ... 4 mm <sup>2</sup>
Color:	Red
Degree of Protection:	acc. to IEC 60529 IP67
Enclosure Material:	Thermoplastic polyester (PBT)
Frequency (f):	60 Hz
Function:	Socket outlet, panel mounting, unified flange, angled
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#416RAU6W
Mounting Type:	unified flange, angled
Number of Poles:	4
Object Classification Code:	2CMT005069
Product Main Type:	TRAU
Product Name:	Industrial Socket Outlet Panel Mounting
Protection Type:	Watertight
Rated Current (I <sub>n</sub> ):	16 A
Rated Voltage (U <sub>r</sub> ):	346 ... 415 V
RoHS Date:	L23
Standards:	IEC 60309-1,-2

<b>Suitable For:</b>	Socket Outlets for Panel Mounting
<b>Suitable for Product Class:</b>	Industrial Plugs and Sockets

---

**Classifications**

<b>E-nummer:</b>	2416712
<b>UNSPSC:</b>	39120000

---

