



STC550E - REV 4 – 07.03.06

**CERTIFICATION CATEGORY II**



# ULTRANE 550 - 551

**CE-Type Examination Certificates**

**ULTRANE 550 : 0075/014/162/12/99/0145**

**ULTRANE 551 : 0075/014/162/12/99/0145 – Ext N° 02/02/01**

**issued by the approved body nr. 0075**

I.F.T.H.– Av. Guy de Collongue - F-69134 ECULLY CEDEX

These gloves conform to the provisions of Directive 89/686/EEC  
for protection against mechanical risks.

57, rue de Villiers - B.P. 190  
92205 NEUILLY SUR SEINE Cedex - FRANCE  
Tél : (33) 1 49.64.22.00 - Fax : (33) 1 49.64.24.29  
[www.mapa-professionnel.com](http://www.mapa-professionnel.com)

**MAPA (U.K.) Ltd**  
Berkeley Business Park  
Wainwright Road – Worcester  
WR4 9ZS - U.K.  
Tel : (44) 0 1905 450300 – Fax: (44) 0 1905 450350

**MAPA®**  
**PROFESSIONNEL**

# ULTRANE 550 - 551

## DESCRIPTION AND GENERAL PROPERTIES

**Polyamide knitted** gloves with palm and fingers coated with **polyurethane foam**.

**Curved fingers** and **contoured palm**.

Guaranteed **silicone-free**.

**Elastic knitted wrist** (natural rubber elastic wrist band).

**Smooth** external surface.

Reference	Coating colour	Textile colour	Sizes available		Corresponding cuff-end colour	Glove length (cm) (nominal values)
Ultrane 550	White	White	S	6	White	21
			M	7	Green	22
			L	8	Grey	24
			XL	9	Yellow	25
			XXL	10	Brown	26
Ultrane 551	Grey	Grey	S	6	White	21
			M	7	Green	22
			L	8	Grey	24
			XL	9	Yellow	25
			XXL	10	Brown	26

These gloves are intended to protect the hand only. They do not protect the wrist or the forearm.

Standard packaging :

- **10** pairs in polyethylene bag with information
- **100** pairs per carton

## "CE"-TYPE EXAMINATION RESULTS



### PROTECTION AGAINST MECHANICAL RISKS

Levels of performance according to EN 388 standard.

4 1 3 1  
| | | |  
| | | ↳ puncture resistance (0 to 4)  
| | ↳ tear resistance (0 to 4)  
| ↳ blade cut resistance (0 to 5)  
↳ abrasion resistance (0 to 4)

The performance levels are determined on the polyurethane coated area of the glove, they may be different on the back of the glove.

These gloves do not protect against chemical risks.

# ULTRANE 550 - 551

## SPECIFIC ADVANTAGES

- Excellent abrasion resistance for enhanced durability.
- Superior breathability thanks to the cellular structure of the polyurethane.
- Enhanced finger sensitivity due to the reduced thickness.
- Hand specific design providing precise fit.
- Comfortable seamless knitliner.

## MAIN FIELDS OF USE

- Intricate assembly work
- Sorting small components
- Handling microprocessors
- Assembling electronic components
- Manufacturing pharmaceutical products
- Processing cosmetics

## INSTRUCTIONS FOR USE

### **For enhanced safety and service life of the gloves :**

- Store the gloves in their original packaging protected from heat, light and humidity.
- It is recommended to check that the gloves are suitable for the intended use, because the conditions of use in the workplace may differ from the tests performed in the laboratory.
- Put the gloves on dry, clean hands.
- Ensure the inside of the gloves is dry before putting them on again.
- Caution : using the gloves or submitting them to a cleaning or laundering process that is not specifically recommended can alter their performance levels.

## DECLARACIÓN DE CONFORMIDAD "CE"

La Empresa

**MAPA s.n.c.**

57, rue de Villiers  
BP 190

92205 Neuilly-sur-Seine Cedex - Francia

declara que los guantes de protección MAPA PROFESSIONNEL

**ULTRANE 550-551-553-554**

**ULTRANE PLUS 557-558**

**ULTRANE GRIP 561-562**

son conformes a los modelos de guantes objeto de los **certificados "CE" de tipo n°**

**ULTRANE 550 : 0075/014/162/12/99/0145**

**ULTRANE 551 : 0075/014/162/12/99/0145 – Ex020201**

**ULTRANE 553 : 1237 ex 1**

**ULTRANE 554 : 0075/014/162/08/04/0155**

**ULTRANE PLUS 557 : 0075/014/162/04/02/0046**

**ULTRANE PLUS 558 : 0075/014/162/04/04/0038**

**ULTRANE GRIP 561 : 0075/014/162/05/04/0073**

**ULTRANE GRIP 562 : 0075/014/162/05/04/0073/Ex010504**

otorgados por el **organismo acreditado n° 0075**

**C.T.C** - F-69367 LYON CEDEX 07

**Ultrane 553 : n° 0321- SATRA** - Rockingham Road – Kettering – NN169JH - UK

Cumplen las disposiciones de la **directiva 89/686/CEE** para proteger contra **riesgos mecánicos**,

y estan fabricados de acuerdo con las **normas europeas EN 420 y EN 388**.

Hecho en Neuilly-sur-Seine, el 13 Septiembre de 2004.

**MAPA**

S.N.C. au Capital de 700.000 F.  
57, rue de Villiers - BP 190  
92205 NEUILLY S/SEINE Cedex  
Siège social : 2, rue de la Harpe, 75008 PARIS  
R.C.S. PARIS B 014 397 720

M. RODOT  
Servicio técnico Clientes