

5PC. 3/8"DR. TUNE UP KIT SET (METRIC & S.A.E.)

PART NO.	CONTENT			G.W.(kg)
09003	5PC.	5	10	13.0


DESCRIPTION:
 1 - Wobble Extension Bar 6"
 1 - Locking Extension Bar 6"
 1 - Bent Flex Head Ratchet Handle
 2 - Metric Spark Plug Sockets 16mm, 21mm



58PC. 3/8"DR. SOCKET SET (METRIC)

PART NO.	CONTENT			G.W.(kg)
09004	58PC.	3	3	13.6

DESCRIPTION:
 18 - 6pt. Metric Sockets 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 24mm
 9 - 6pt. Metric Deep Sockets 8, 10, 11, 12, 13, 14, 15, 17, 19mm
 2 - Spark Plug Sockets 16, 21mm
 24 - Bit Sockets
 Slotted 5.5, 6.5, 8.0mm
 Phillips #1, #2, #3
 Pozidriv #1, #2
 Torx® 10, 15, 20, 25, 30, 40, 45, 50, 55
 Hex 3, 4, 5, 6, 7, 8, 10
 5 - Accessories
 Quick-Release Ratchet
 Wobble Extension Bars 3", 10"
 Universal Joint
 1/2"Fx3/8"M 3-Way Adapter



47PC. 3/8"DR. SOCKET SET (METRIC & S.A.E.) **New**

PART NO.	CONTENT			G.W.(kg)
09016	47PC.	3	3	19.6

DESCRIPTION:
 18 - 6pt. Metric Sockets 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 24mm
 9 - 6pt. Metric Deep Sockets 8, 10, 11, 12, 13, 14, 15, 17, 19mm
 2 - Spark Plug Sockets 5/8", 13/16"
 11 - 6pt. S.A.E. Sockets 1/4", 5/16", 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8"
 7 - Accessories
 Quick-Release Ratchet
 Wobble Extension Bars 3", 6", 10"
 Flex Handle 8"
 Universal Joint
 1/2"Fx3/8"M 3-Way Adapter



16PC. 3/8"DR. SOCKET SET (S.A.E.)

PART NO.	CONTENT			G.W.(kg)
09085	16PC.	6	12	25.6

DESCRIPTION:
 11 - 6pt. S.A.E. Sockets 1/4", 5/16", 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8"
 5 - Accessories
 Quick-Release Ratchet
 Wobble Extension Bars 3", 6"
 Flex Handle 8"
 1/2"Fx3/8"M 3-Way Adapter



14PC. 3/8"DR. SOCKET SET (METRIC) **New**

PART NO.	CONTENT			G.W.(kg)
09523	14PC.	4	16	15.6

DESCRIPTION:
 12 - 6pt. Metric Sockets 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm
 2 - Accessories
 Quick-Release Ratchet
 Wobble Extension Bars 3"



26PC. 3/8"DR. SOCKET TOOL SET (METRIC)

PART NO.	CONTENT			G.W.(kg)
09089	26PC.	4	4	17.5

DESCRIPTION:
 7 - 6pt. Metric Sockets 10, 11, 12, 13, 14, 17, 19mm
 3 - 50L Bit Sockets Hex 8, 10, 12mm
 3 - 100L Bit Sockets Torx® 30, 40, 50mm
 2 - Spark plug Sockets 16, 21mm
 2 - Screwdrivers Slotted 6x100mm Phillips #2x100mm
 9 - Accessories
 Quick-Release Ratchet
 Wobble Extension Bars 5"
 Sliding T-Bar
 Slip Joint Pliers 8"
 Combination Wrenches 10, 12, 13, 14, 17mm



21PC. 3/8"DR. SOCKET TOOL SET (METRIC)

PART NO.	CONTENT			G.W.(kg)
09503	21PC.	3	3	19.8

DESCRIPTION:
 12 - 6pt. Metric Sockets 6, 7, 8, 10, 12, 13, 14, 17, 19, 21, 22, 24mm
 2 - Screwdrivers Slotted 6x100mm Phillips #2x100mm
 7 - Accessories
 Wobble Extension Bars 3", 10"
 Flex Handle 8"
 Sliding T-Bar
 Universal Joint
 Flex Shaft
 Energy Saving Linesman 8"



9PC. 3/8"DR. MOTORCYCLE REPAIR SET (METRIC)

PART NO.	CONTENT			G.W.(kg)
09511	9PC.	6	6	8.5

DESCRIPTION:
 7 - 6pt. Metric Deep Sockets 8, 9, 10, 11, 12, 13, 14mm
 2 - Accessories
 Sliding T-Bar
 Wobble Extension Bars 10"



20PC. 1/2"DR. SOCKET SET (METRIC)

PART NO.	CONTENT			G.W.(kg)
09005	20PC.	6	6	20.9

DESCRIPTION:
 12 - 6pt. Metric Sockets 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 22, 24mm
 3 - 6pt. Metric Deep Sockets 13, 17, 19mm
 1 - Spark Plug Socket 16mm
 4 - Accessories
 Quick-Release Ratchet
 Wobble Extension Bar 10"
 Universal Joint
 3/8"Fx1/2"M 3-Way Adapter



46PC. 1/2"DR. SOCKET SET (METRIC & S.A.E.)

PART NO.	CONTENT			G.W.(kg)
09006	46PC.	3	3	19.9

DESCRIPTION:
 20 - 6pt. Metric Sockets 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 27, 30, 32mm
 7 - 6pt. Metric Deep Sockets 10, 12, 13, 14, 15, 17, 19mm
 2 - Spark Plug Sockets 16, 21mm
 11 - 6pt. S.A.E. Sockets 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8", 15/16", 1"
 6 - Accessories
 Quick-Release Ratchet
 Flex Handle 10"
 Wobble Extension Bars 5", 10"
 Universal Joint
 3/8"Fx1/2"M 3-Way Adapter



58PC. 1/2"DR. SOCKET SET (METRIC)

PART NO.	CONTENT			G.W.(kg)
09007	58PC.	3	3	22.7

DESCRIPTION:
 17 - 6pt. Metric Sockets 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 24, 27, 30, 32mm
 8 - 6pt. Metric Deep Sockets 10, 11, 12, 13, 14, 15, 17, 19mm
 2 - Spark Plug Socket 16, 21mm
 25 - 5/16"Shank 30L Bits
 Slotted 8, 10, 12
 Phillips #1, #2, #3, #4
 Pozidriv #1, #2, #3, #4
 Torx® 20, 25, 30, 40, 45, 50, 55
 Hex 4, 5, 6, 8, 10, 12, 14mm
 6 - Accessories
 Quick-Release Ratchet
 5/16"Shank x1/2"Dr. Bit Coupler
 Wobble Extension Bars 5", 10"
 Universal Joint
 3/8"Fx1/2"M 3-Way Adapter



24PC. 1/2"DR. SOCKET SET (METRIC)

PART NO.	CONTENT			G.W.(kg)
09060	24PC.	4	4	20.0
09060-6	24PC.	4	4	20.0

DESCRIPTION: (09060)
 19 - 12pt. Metric Sockets 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 27, 30, 32mm
 5 - Accessories
 Quick-Release Ratchet
 Wobble Extension Bars 5", 10"
 Universal Joint
 Sliding T-Bar
 DESCRIPTION: (09060-6)
 19 - 6pt. Metric Sockets 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 27, 30, 32mm
 5 - Accessories
 Quick-Release Ratchet
 Wobble Extension Bars 5", 10"
 Universal Joint
 Sliding T-Bar

