



283 N/B8

Set of eight offset bihexagonal ring wrenches

- 283 N/6x7-8x9-10x11-12x13-14x15-16x17-18x19-20x22 mm
- Supplied in plastic wallet

kg	code	
1,5	02830311	1



283 N/R13

Set of thirteen offset bihexagonal ring wrenches

- 283 N/6x7-8x9-10x11-12x13-14x15-16x17-18x19-20x22-21x23-24x26-25x28-27x29-30x32 mm
- Supplied with metal holder

kg	code	
4,2	02830314	1

283 RV13

Empty holder for double ended offset ring wrenches

- Enamelled sheet steel

L mm	gr	code	
390	270	283600	1



283 N/S13

Set of thirteen offset bihexagonal ring wrenches

- 283 N/6x7-8x9-10x11-12x13-14x15-16x17-18x19-20x22-21x23-24x26-25x28-27x29-30x32 mm
- Supplied with metal display stand

kg	code	
4,7	02830317	1

283 SV13

Empty metal display stand

gr	code	
400	002520012	1



283 NP

Double ended offset bihexagonal ring wrenches, inch sizes

mm	L mm	code	
1/4x5/16	172	02830201	2
3/8x7/16	197	02830203	2
1/2x9/16	238	02830205	2
9/16x5/8	238	02830206	2
5/8x11/16	258	02830207	2
5/8x3/4	258	02830208	2
25/32x13/16	316	02830210	2
7/8x15/16	324	02830211	2
15/16x1	328	02830212	2
1 1/16 x 1 1/8	353	02830214	2
1 3/16 x 1 5/16	402	02830216	2
1 3/8 x 1 1/2	440	02830217	2

283 NP/SE7

Set of seven offset bihexagonal ring wrenches

- 283 NP/ 1/4x5/16-3/8x7/16-1/2x9/16-9/16x5/8-5/8x3/4-25/32x13/16-7/8x15/16-15/16x1"

kg	code	
2	02830326	1

283 NP/SE12

Set of twelve offset bihexagonal ring wrenches

- 283 NP/ 1/4x5/16-3/8x7/16-1/2x9/16-9/16x5/8-5/8x11/16-5/8x3/4-25/32x13/16-7/8x15/16-15/16x1-1 1/16x1 1/8-1 3/16x1 5/16-1 3/8x1 1/2"


kg	code	
4,8	02830322	1



284

Double ended offset bihexagonal ring wrench for scaffolds

O mm	L mm	code	
21x22	315	284101	5



285

ISO 1711/1 UNI 6741
ISO 7738 DIN 3113 SAE AS 954E

Combination wrenches

- Thin open end angled at 15°
- Ergonomic grip
- Bihexagonal head bent at 15°

O mm	L mm	b mm	code	
5,5	115	3,5	02850700	5
6	115	3,5	02850701	5
7	122	3,7	02850702	5
8	133	4,0	02850703	5
9	138	4,0	02850704	5
10	145	4,4	02850705	5
11	155	4,5	02850706	5
12	162	4,7	02850707	5
13	170	5,1	02850708	5
14	180	5,2	02850709	5
15	185	5,5	02850710	5
16	195	6,0	02850711	5
17	202	6,1	02850712	5
18	208	6,5	02850713	5
19	216	6,7	02850714	5
20	224	6,8	02850715	1
21	233	7,1	02850716	1
22	248	7,3	02850717	5
23	257	7,5	02850718	1
24	267	7,8	02850719	5
25	274	8,0	02850720	1
26	285	8,3	02850721	1
27	295	8,4	02850722	1
28	305	8,6	02850723	1
29	320	9,0	02850724	1
30	340	9,2	02850725	1
32	355	9,7	02850726	1
34	390	9,9	02850727	1
35	430	10,4	02850728	1
36	440	10,6	02850729	1
38	450	11,4	02850730	1
41	460	12,4	02850731	1

285 SE17

Set of seventeen combination wrenches

- 285/6-7-8-9-10-11-12-13-14-15-16-17-18-19-20-21-22 mm

kg	code	
1,6	285860	1

285 SE26

Set of twenty-six combination wrenches

- 285/6-7-8-9-10-11-12-13-14-15-16-17-18-19-20-21-22-23-24-25-26-27-28-29-30-32 mm

kg	code	
4,9	285861	1