



Basic series with elevated
switching distance
4 mm embeddable



Switching element function	PNP	Make function
Rated operating distance s_n	4 mm	
Installation	embeddable	
Assured operating distance s_a	0 ... 3,24 mm	
Reduction factor r_{AI}	0,45	
Reduction factor r_{Cu}	0,35	
Reduction factor r_{V2A}	0,7	
Operating voltage U_B	10 ... 30 V	
Switching frequency f	0 ... 1000 Hz	
Hysteresis H	typ. 5 %	
Reverse polarity protection	yes	
Short circuit protection	pulsing	
Voltage drop U_d	≤ 3 V	
Rated insulation voltage U_{BIS}	500 V	
Operating current I_L	0 ... 150 mA	
Off-state current I_r	0 ... 0,5 mA typ.	
No-load supply current I_0	≤ 15 mA	
Indication of the switching state	ring LED, yellow	
Standards	EN 60947-5-2	
Ambient temperature	-25 ... 70 °C (248 ... 343 K)	
Connection type	2 m, PVC cable	
Cable version	PBT	
Core cross-section	0.14 mm ²	
Housing material	brass, nickel-plated	
Sensing face	PBT	
Protection degree	IP67	
Mass	30 g	

Connection_type:



087741_ENG.xml

2003-03-25