

EUDA-S1910

19" Intel Atom N270 based Fanless Panel PC



66.7 mm (26.3")



38.8 mm (15.3")


FEATURES

- Slim and long MTBF 19" Industrial grade fanless panel PC
- Built-in 5-wire Resistive Touch Screen
- VESA, Panel, Openframe mounting support
- Aluminum front panel meet with IP65 Certification
- Vibration & Shock Test (15G peak acceleration, 11m sec)

CPU	Intel® Atom™ N270 1.6GHz Processor
Chipset	Intel® 945GSE + ICH7M
Memory	Up to 2GB DDR2 (SO-DIMM)
Storage	2.5" SATA HDD
Solid State Disk	Compact Flash up to 32GB
VGA	Intel® GMA 950 Graphics
Ethernet	Realtek® Gigabit Ethernet
Audio	Realtek HD Audio Codec
I/O	- 2x RS232 - 4x USB 2.0 port - 1x Lin-out, 1x MIC port - 1x VGA port - 1x Gigabit Ethernet port - 1x CF Slot
Touch screen	5-wire Resistive type
LCD	- Size: 19" - Resolution: 1280x1024 - Brightness: 250 cd/m ² - Contrast Ratio: 1000:1 - Backlight MTBF: 50000 hrs
Expansion function	TBA
Operation Temp.	0~50°C degree
Storage Temp.	-20~80°C degree
Relative Humidity	5~95%, non-condensing
Weight	8.3 Kg

Dimensions	463(w) x 392(H) x 67 (D)mm
Mounting	VESA 75x75, 100x100, Panel Mount
Power Supply	DC12V
Front Panel Protection	IP65 Compliant
Certificate	CE/FCC Class B

REAR I/O



ORDERING GUIDE

- EUDA-S19 10-000-00
Basic 19" panel PC