

GT3-OSL SERIES FOR OSRAM OSLOM SSL/SX LEDS



OSRAM
www.osram.com



- Special care taken to make a uniform white or warm white illumination.
- Lens material optical grade PMMA with high UV and temperature resistance (105°C/220°F). Allows use of high current and temperature conditions
- Best available optical efficiency, up to 90%.
- No lens holder. Fastening to heat sink with droplets of glue
- Please check fastening details from this link:
(http://www.ledil.com/datasheets/DataSheet_GLUES.pdf)

LENS TYPES


NAME	ORDERING CODE	FWHM
GT3-OSL Spot	C10891_GT3-OSL-S	±8.5°
GT3-OSL Medium	C10892_GT3-OSL-M	±14°
GT3-OSL Wide	C10893_GT3-OSL-W	±18°
GT3-OSL WW	C11624_GT3-OSL-WW	±26°

NAME	ORDERING CODE	FWHM
GT3-OSL Spot	C10891_GT3-OSL-SX-S	to be measured shortly
GT3-OSL Medium	C10892_GT3-OSL-SX-M	to be measured shortly
GT3-OSL Wide	C10893_GT3-OSL-SX-W	to be measured shortly
GT3-OSL WW	C11624_GT3-OSL-SX-WW	to be measured shortly

© Ledil Oy – PRELIMINARY - Subject to change without prior notice


MEASUREMENT DATA

Relative intensity of C10891_GT3-OSL-S




© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Relative Intensity of C10892_GT3-OSL-M





© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Relative intensity of C10893_GT3-OSL-W




© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Relative intensity of C11624_GT3-OSL-WW



© Ledil Oy – PRELIMINARY - Subject to change without prior notice

DRAWINGS



© Ledil Oy – PRELIMINARY - Subject to change without prior notice