




1.1 FREQUENCY RANGE: DC-4 GHz
1.2 NOMINAL IMPEDANCE: 75 OHM
1.3 WORKING VOLTAGE: 500 VOLTS MAX.
1.4 PROOF VOLTAGE: 1600 VOLTS
1.5 VSWR: 1.1 MAX.

2.1 BODIES: BRASS PER JIS-C3604
2.2 CENTER CONTACT: BRASS PER JIS-C3604
2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
2.4 CRIMP FERRULE: BRASS PER JIS-C2700


SEE BELOW TABLE FOR DETAILS

4.1 FOR USE WITH 7731A OR SIMILAR STYLE CABLE

4.2 CABLE ATTACHMENT: OUTER: CRIMP, INNER: SOLDER/CRIMP

4.3 CRIMP SIZE REQUIRED: CONTACT: 1.8(.071) HEX. CRIMP TOOL
FERRULE: 10.9(.429) HEX. CRIMP TOOL

5.1 OPERATING TEMPERATURE RANGE: -66° C TO +165° C



STRIPPING DIMENSION

9	CRIMP FERRULE	BRASS	1	NICKEL
8	CENTER CONTACT	BRASS	1	GOLD
7	BODY	BRASS	1	NICKEL 100 μ " MIN.
6	WASHER	BRASS	1	NICKEL
5	SPRING WASHER	BERYLLIUM COPPER	1	NONE
4	WASHER	BRASS	1	NICKEL
3	GASKET	SILICONE	1	RED
2	INSULATION	TEFLON	1	NONE
1	SHELL	ZINC	1	NICKEL
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH



APPROVED

by DATE:

DESCRIPTION		BNC STRAIGHT PLUG CRIMP									
製圖	DRAWN	TOLERANCE		品名		13-10-73		T.G.Z		DATE	REV.
	Yoko	.X	±0.2	TITLE		ROHS COMPLIANT		(750)			
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO.		13-0235			
	Arc	.XXX	±0.05		mm(In)						
認定	APPROVAL	.XXX	±0.05	比例	SCALE						
	Lewis	ANGLE	±5°		4:1						