



# Product datasheet

ENGLISH



## Gripfoot

### Grit Tape, Cleats and Tiles for Slip-Resistance

- Abrasive grit 'anti-slip' products with self-adhesive backing available in tapes, cleats and tiles.
- Provides additional grip underfoot on smooth surfaces.
- Hard wearing and easy to install
- Gripfoot Tape – versatile for floor surfaces, machinery, vehicles and marine use.
- Gripfoot Cleats (rectangular) are designed for use on steps and stairs.
- Gripfoot Tiles (square) are ideal for increasing safety on smooth, tiled floors.
- Hazard version (tape only) in yellow/black provides high visibility in darkness or low light conditions.
- Conforms to Slip Resistant Test EN 13552 Category R13.

Dimensions (m.)	Weight Kg	Packaging Dimensions (cm.)	Packaging Type	Packaging Volume (m.)	Packaging Quantity	Colour	Part Code
25mm x 18.3m	0.40	15 x 16 x 2.5	Jiffy Bag	1	27	Black	GF010001
50mm x 18.3m	0.85	20 x 26 x 6	Jiffy Bag	1	27	Black	GF010002
102mm x 18.3m	1.55	20 x 33 x 11	Jiffy Bag	1	27	Black	GF010003
152mm x 18.3m	2.35	20 x 20 x 16	Jiffy Bag	1	27	Black	GF010004
140mm x 140mm	0.75	18 x 66 x 1.5	Jiffy Bag	10	N/A	Black	GF010005
152mm x 610mm	0.15	18 x 20 x 1.5	Jiffy Bag	10	N/A	Black	GF010006
50mm x 18.3m			Jiffy Bag			Black/Yellow	GF010702

**Material:** Abrasive grit consisting of aluminium oxide bonded to a polymer substrate. Solvent based acrylic emulsion adhesive backing. Product supplied with a moisture resistant release liner.

**Typical Applications:** Suitable for stairs, ladders, ramps, walkways, vehicles and boats.

**Surface Finish:** Grit

**Grit size:** 46 grit

**Thickness:** 1.0+ ± 0.05mm

**Resistance to Chemicals:** N/A

**Environmental Resistance:** Suitable for indoor and outdoor environments

**UV Resistance:** Yes

**Installation Method:** Pressure sensitive self-adhesive tape

**Product Performance:** Conforms to slip resistance test EN13552 Category R13

#### Adhesion Properties

**Rolling Ball Tack** 20cm

**Shear Resistance** 24 hrs (1" X 1" @ 1 kg)

**Coating Thickness** 0.05 mm

**Solvent Residual** >0.5 %

**Adhesion** 2.5 kg/1"



Release Force 13 g/m<sup>2</sup>  
Dry Coating Weight 37 g/m<sup>2</sup>  
Operation Temperature 10 °c +  
Safe Temperature Range -10 °c to +60 °c  
Adhesive Type Acrylic Adhesive

**Web Properties**

Property	Grit Carrier Substrate	Release Liner
Web Type	PVC Film	Release Liner
Basic Weight	181 g/m <sup>2</sup>	120 g/m <sup>2</sup>
Thickness	0.15 mm	0.185 mm
Tensile Strength	MD: 4.2 kg/15mm	MD: 8.7 kg/25mm
	CD: 3.1 kg/15mm	CD: 5.7 kg/25mm
Color	Black	Brown
Smoothness	Good	Good
Elongation	200±25%	
Die Cutting	Good	Good

Country of Origin: Taiwan