



ISO view



Side view

### Bracket

- ▶ Pressed steel plate with khaki powder coating
- ▶ Aluminum die-casting bracket with bi-level balls upon ball seats in the swivel head
- ▶ High quality ABS resin handle, two side access to level
- ▶ NBR resin cushion to stand, anti-vibration function
- ▶ Ivory texture powder coating and zinc-galvanized

### Wheels

- ▶ High quality nylon
- ▶ High abrasion resistance, shock and impact-resistant, corrosion-resistant, high chemical resistance to alcohol, salts and certain acids, black color
- ▶ No bearing

### Technical Data

Wheel Diameter	63 mm
Width of Tread	28 mm
Hardness of Tread	70 Shore D
Size of Plate	90 x 90 mm
Plate Hole Centers	70 x 70 mm
Plate Hole	9 mm
Leveling Extent	15 mm
Offset	46 mm
Overall Height	103 mm
Temperature	-10 ~ +90°C
Load Capacity / 1pcs	500 kg
Load Capacity / 4pcs	1,000 kg

