



Consult Heyco for Colors Other Than Black or White


Heyco® Dome Plugs

- Closes unneeded panel holes.
- Convex, matte finish head tapers to thin edge (Except DP-187).
- Twenty-nine sizes for use in 3/16" (4,7mm) to 6" (152,4mm) diameter holes.
- Locks firmly into panel up to 1/4" (6,4mm) thick.
- Quick and easy installation.

LabKit No. 3 (Part #2997)

Perfect for product design departments, experimental labs, and for all prototype work. LabKit contains an assortment of the most popular sizes of hole, vent, and pry out plugs. Pertinent information on each size is attached inside the box lid.

See page 3-33 for more details.



| PANEL DIMENSIONS | | | | PART NO. | | DESCRIPTION | PART DIMENSIONS | | | |
|-------------------|-----|------------------------|-------|----------|-------|-------------|-----------------|-------|------------------|------|
| Maximum Thickness | | Mounting Hole Diameter | | Black | White | | A Head Diameter | | B Overall Height | |
| in. | mm. | in. | mm. | | | in. | mm. | in. | mm. | |
| .062 | 1,6 | .187 | 4,7 | *2590 | *2591 | ** DP-187 | .250 | 6,4 | .234 | 5,9 |
| .062 | 1,6 | .250 | 6,3 | 2603 | 2604 | ** DP-250 | .312 | 7,9 | .312 | 7,9 |
| .062 | 1,6 | .312 | 7,9 | 2613 | 2614 | ** DP-312 | .375 | 9,5 | .312 | 7,9 |
| .125 | 3,2 | .375 | 9,5 | 2617 | 2618 | DP-375 | .468 | 11,9 | .406 | 10,3 |
| .125 | 3,2 | .437 | 11,1 | 2633 | 2634 | DP-437 | .531 | 13,5 | .406 | 10,3 |
| .125 | 3,2 | .500 | 12,7 | 2643 | 2644 | DP-500 | .578 | 14,7 | .406 | 10,3 |
| .125 | 3,2 | .562 | 14,3 | 2653 | 2654 | DP-562 | .656 | 16,7 | .406 | 10,3 |
| .125 | 3,2 | .625 | 15,9 | 2663 | 2664 | DP-625 | .718 | 18,2 | .406 | 10,3 |
| .125 | 3,2 | .687 | 17,4 | 2673 | 2674 | DP-687 | .781 | 19,8 | .406 | 10,3 |
| .125 | 3,2 | .750 | 19,1 | 2683 | 2684 | DP-750 | .921 | 23,4 | .406 | 10,3 |
| .125 | 3,2 | .812 | 20,6 | 2693 | 2694 | DP-812 | .890 | 22,6 | .406 | 10,3 |
| .125 | 3,2 | .875 | 22,2 | 2703 | 2704 | DP-875 | 1.015 | 25,8 | .453 | 11,5 |
| .125 | 3,2 | 1.000 | 25,4 | 2713 | 2714 | DP-1000 | 1.203 | 30,6 | .453 | 11,5 |
| .125 | 3,2 | 1.093 | 27,8 | | | | | | | |
| | | 1.125 | 28,6 | 2723 | 2724 | DP-1093 | 1.218 | 30,9 | .453 | 11,5 |
| .125 | 3,2 | 1.187 | 30,1 | 2733 | 2734 | DP-1187 | 1.312 | 33,3 | .453 | 11,5 |
| .125 | 3,2 | 1.250 | 31,7 | 2740 | 2741 | DP-1250 | 1.375 | 34,9 | .453 | 11,5 |
| .125 | 3,2 | 1.375 | 34,9 | 2753 | 2754 | DP-1375 | 1.500 | 38,1 | .453 | 11,5 |
| .125 | 3,2 | 1.500 | 38,1 | 2763 | 2764 | DP-1500 | 1.671 | 42,4 | .453 | 11,5 |
| .125 | 3,2 | 1.750 | 44,5 | 2773 | 2774 | DP-1750 | 1.906 | 48,4 | .453 | 11,5 |
| .125 | 3,2 | 2.000 | 50,8 | 2783 | 2784 | DP-2000 | 2.170 | 55,1 | .469 | 11,9 |
| .250 | 6,4 | 2.093- | 53,2 | | | | | | | |
| | | 2.125 | 54,0 | 2403 | 2404 | DP-2.093 | 2.343 | 59,9 | .760 | 19,3 |
| .250 | 6,4 | 2.250 | 57,2 | 2411 | 2412 | DP-2.25 | 2.479 | 63,0 | .750 | 19,1 |
| .250 | 6,4 | 2.500 | 63,5 | 2790 | 2791 | DP-2.5 | 2.718 | 69,0 | .750 | 19,1 |
| .250 | 6,4 | 3.000 | 76,2 | 2455 | 2456 | DP-3.0 | 3.171 | 80,5 | .750 | 19,1 |
| .250 | 6,4 | 3.375 | 85,7 | 2482 | 2483 | DP-3.375 | 3.656 | 92,9 | .750 | 19,1 |
| .250 | 6,4 | 3.500 | 88,9 | 2464 | 2465 | DP-3.5 | 3.656 | 92,9 | .750 | 19,1 |
| .250 | 6,4 | 4.000 | 101,6 | 2473 | 2474 | DP-4.0 | 4.156 | 105,6 | .750 | 19,1 |
| .250 | 6,4 | 5.000 | 127,0 | 2451 | 2452 | DP-5.0 | 5.219 | 132,5 | .781 | 19,8 |
| .250 | 6,4 | 6.000 | 152,4 | 2453 | 2454 | DP-6.0 | 6.219 | 157,9 | .781 | 19,8 |

Standard Colors: Black or White. Consult factory for color matching, prices, and minimum order quantities.

Locking fingers in fractional increments up to the maximum panel thickness.

*Convex, glossy finish head tapers to thin edge.

Approximate Head Thickness: .063" (1,6mm). Thickness may vary.

**Depicts single panel thickness.

Quick Specs

| | |
|----------------------------|---|
| Material | 6/6 "Nylon" |
| Certifications | Recognized under the Component Program of Underwriters' Laboratories File #E-15331 Certified by the Canadian Standards Association File #LR-8919 |
| Flammability Rating | 94V-2 |
| Material Temperature Index | 125°C—Maximum temperature on part not to exceed 105°C |