


THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		N	REV PER ECN 0G3B-03B3-03	21AUG03	SC	JE



1. PARTS COMPLY WITH AMP SOLDERABILITY SPEC 109-11-3.
2. PARTS CAPABLE OF BEING APPLIED BY AMPOMATOR.
3. WIRE RANGE: 0.12-0.4mm² (26-22 AWG).
4. INSULATION RANGE: 1.52-2.54 [.060-.100] DIA
5. 0.00508 [.000200] MIN BRIGHT TIN-LEAD.
6. DIMENSIONS IN BRACKETS ARE IN INCHES.
7. 0.00508 [.000200] MIN BRIGHT TIN.



7	0.20[.008] PHOS BRONZE	3-640108-1
5	0.20[.008] PHOS BRONZE	640108-1
FINISH	MATERIAL	PART NO.

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 21AUG2003	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105			
DIMENSIONS: INCHES		CHK J. ELLIS 21AUG2003				
		APVD J. ELLIS 21AUG2003	NAME MINI AMP-IN™			
		PRODUCT SPEC				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC				
0 PLC ±		114-1016				
1 PLC ±		WEIGHT				
2 PLC ± 0.13 [.005]		CUSTOMER DRAWING				
3 PLC ±		SCALE 10:1				
4 PLC ±		SHEET 1 OF 1				
ANGLES ±		REV N				
FINISH						
SEE TABLE						