

THIS DRAWING IS UNPUBLISHED.





RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	ECN	DATE	APVD
J	-		A	RELEASED		23AUG2005	T.K D.M
			A1	PART NO ADDITION	ECR-07-005648	22MAR2007	M.M D.M
			A2	DRAFTING ERROR	ECR-07-025215	23OCT2007	M.M S.M
			B	REVISED	ECR-08-028241	07NOV2008	M.M A.O



40POS(X-KEY): 1-1827863-0

1. MATERIAL: GLASS FILLED THERMO PLASTIC POLYESTER(94V-0), COLOR: BLACK
2. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.
3. THE KEYING ARRANGEMENT OF "Y" IS SYMMETRIC WITH "X".

1. 材料: ガラス入り熱可塑性ポリエステル樹脂(94V-0), 色: 黒
2. 文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません。
3. Y KEY形状はX KEY形状と左右対称

40	Y	19	38.0	40.9	42.6	2-1827863-0
40	X	19	38.0	40.9	42.6	1-1827863-0
34	Y	16	32.0	34.9	36.6	2-1827863-7
34	X	16	32.0	34.9	36.6	1-1827863-7
32	X	15	30.0	32.9	34.6	1-1827863-6
30	X	14	28.0	30.9	32.6	1-1827863-5
28	X	13	26.0	28.9	30.6	1-1827863-4
26	Y	12	24.0	26.9	28.6	2-1827863-3
26	X	12	24.0	26.9	28.6	1-1827863-3
24	X	11	22.0	24.9	26.6	1-1827863-2
22	X	10	20.0	22.9	24.6	1-1827863-1
POS	KEY	n	A	B	C	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN T. KUDO 16MAR2005	Tyco Electronics AMP K.K. Kawasaki, Japan	
DIMENSIONS: 単位: ㎜		CHK D. MITSUGI 23AUG2005	NAME DYNAMIC D1100D 2.0mmPITCH REC HSG 22-40POS	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±5° 0-PLC ± 1-PLC ±0.5 2-PLC ±0.13 3-PLC ±0.013 4-PLC ±0.001 ANGLES ±		APVD D. MITSUGI 23AUG2005	DRAWING NO 114-5377	
MATERIAL 材料		PRODUCT SPEC 製品規格 108-78268, 78298	RESTRICTED TO	
FINISH 仕上		APPLICATION SPEC 取付適用規格 114-5377	SIZE A3	
		WEIGHT	CAGE CODE 00779	
		CUSTOMER DRAWING	DRAWING NO C=1827863	
		SCALE 尺度 2:1	SHEET 1 OF 3	
			REV B	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR
















DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1 OF 3



22POS(X-KEY): 1-1827863-1

26POS(X-KEY): 1-1827863-3







28POS(X-KEY): 1-1827863-4

30POS(X-KEY): 1-1827863-5

32POS(X-KEY): 1-1827863-6

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN T. KUDO 16MAR2005 CHK D. MITSUGI 23AUG2005 APVD D. MITSUGI 23AUG2005 PRODUCT SPEC 108-78268, 78298 APPLICATION SPEC 114-5377 WEIGHT - CUSTOMER DRAWING		Tyco Electronics AMP K.K. Kawasaki, Japan NAME DYNAMIC D1100D 2.0mmPITCH REC HSG 22-40POS SIZE A3 CAGE CODE 00779 DRAWING NO C=1827863 RESTRICTED TO - SCALE 2:1 SHEET 2 OF 3 REV B	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH -			

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
J	-			SEE SHEET 1 OF 3		



34POS(X-KEY): I-1827863-7

24POS(X-KEY): I-1827863-2

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN T. KUDO 16MAR2005		Tyco Electronics AMP K.K. Kawasaki, Japan	
DIMENSIONS: mm		CHK D. MITSUGI 23AUG2005			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. MITSUGI 23AUG2005	
		0 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		NAME DYNAMIC D1100D 2.0mmPITCH REC HSG 22-40POS	
MATERIAL -		FINISH -		PRODUCT SPEC 108-78268, 78298	
		APPLICATION SPEC 114-5377		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
		WEIGHT -		A 300779 C-1827863	
		CUSTOMER DRAWING		SCALE 2:1 SHEET 3 OF 3 REV B	