


## Cam followers



Dimensions				Basic load ratings		Fatigue load limit	Maximum radial loads		Limiting speed	Mass	Designation
D	d	B	C	dynamic C	static C <sub>0</sub>	P <sub>u</sub>	dynamic F <sub>r</sub>	static F <sub>0r</sub>	r/min	kg	-
mm				kN		kN	kN				
19	8	32	11	3,47	3,8	0,415	3,8	5,5	5600	0,029	KR 19 PPA



**Appertaining grease nipple(s)** NIP A1

**Appertaining hexagonal nut**  
 Size, mm M 8  
 Rec. tightening torque, Nm 8