


OPENING FOR CABLE
(SEE DASH NO. FOR DIA.)



1. PARTS PACKAGED UNASSEMBLED, AS A UNIT KIT.
2. ZINC PLATED .000200-.000400 THICK, CLEAR CHROMATE COATING.


SIZE IDENTIFICATION LETTER
MOLDED IN APPROXIMATE AREA
SHOWN, SEE TABLE

#4-40 HEX NUT
(QTY. 2)
MATL: CARBON STEEL
FINISH: 2

#4-40 FIL HD SCREW
(QTY. 2)
MATL: STEEL
FINISH: 2


AMP LOGO

TEXTURED
FINISH



CABLE CLAMP HALF
(QTY. 2)
MATL: ZINC ALLOY
FINISH: NICKEL OVER COPPER

#4-40 MOUNTING SCREW
(QTY. 2)
MATL: CARBON STEEL
FINISH: 2



D	.280	5745173-5
G	.350	5745173-4
K	.430	5745173-3
M	.480	5745173-2
P	.530	5745173-1
NECK SIZE IDENT	MAX CABLE DIA	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER 12AUG05	tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm		CHK C. ROHDE 12AUG05		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. WALMSLEY 12AUG05	NAME CABLE CLAMP KIT, SIZE 3, 180 DEGREE, AMPLIMITE	
MATERIAL SEE CALLOUTS		PRODUCT SPEC —	SIZE A2	
FINISH SEE CALLOUTS		APPLICATION SPEC —	CAGE CODE 00779	
		WEIGHT —	DRAWING NO G-5745173	
		CUSTOMER DRAWING	RESTRICTED TO —	
		SCALE 1:1	SHEET 1 OF 1	
			REV 0	