


- MP-X Drill Short
- MP-X Spiralbohrer, kurz
- MP-X Spiraalboren
- Foret MP-X
- Broca MP-X, short
- Broca MP-X Curta



R457



- 1.1 1.2 1.3 1.4 1.5 1.6 2.1 2.2 3.1 3.2 3.3 3.4 4.1 4.2 4.3 6.1 6.2 6.3 6.4 7.1
- 7.2 7.3 7.4
- 2.3

d ₁ Ø	d ₁ Ø	d ₁ decimal	l ₂	l ₁	l ₃	d ₂ Ø	e-Code
Inch	mm	Inch	mm	mm	mm	mm	
1/8	3.00	0.1181	20	62	36	6	R4573.0
	3.10	0.1220	20	62	36	6	R4573.1
	3.17	0.1248	20	62	36	6	R4571/8
	3.20	0.1260	20	62	36	6	R4573.2
	3.30	0.1299	20	62	36	6	R4573.3
	3.40	0.1339	20	62	36	6	R4573.4
	3.50	0.1378	20	62	36	6	R4573.5
9/64	3.57	0.1406	20	62	36	6	R4579/64
	3.60	0.1417	20	62	36	6	R4573.6
	3.70	0.1457	20	62	36	6	R4573.7
	3.80	0.1496	24	66	36	6	R4573.8
	3.90	0.1535	24	66	36	6	R4573.9
5/32	3.97	0.1563	24	66	36	6	R4575/32
	4.00	0.1575	24	66	36	6	R4574.0
	4.05	0.1594	24	66	36	6	R4574.05
	4.10	0.1614	24	66	36	6	R4574.1
	4.20	0.1654	24	66	36	6	R4574.2
	4.30	0.1693	24	66	36	6	R4574.3
11/64	4.37	0.1720	24	66	36	6	R45711/64
	4.40	0.1732	24	66	36	6	R4574.4
	4.50	0.1772	24	66	36	6	R4574.5
	4.60	0.1811	24	66	36	6	R4574.6
	4.70	0.1850	24	66	36	6	R4574.7
3/16	4.76	0.1874	28	66	36	6	R4573/16
	4.80	0.1890	28	66	36	6	R4574.8
	4.90	0.1969	28	66	36	6	R4574.9
	5.00	0.1969	28	66	36	6	R4575.0
	5.05	0.1988	28	66	36	6	R4575.05
	5.10	0.2008	28	66	36	6	R4575.1
13/64	5.16	0.2031	28	66	36	6	R45713/64
	5.20	0.2047	28	66	36	6	R4575.2
	5.50	0.2165	28	66	36	6	R4575.5
7/32	5.56	0.2189	28	66	36	6	R4577/32
	5.60	0.2205	28	66	36	6	R4575.6
	5.70	0.2244	28	66	36	6	R4575.7
	5.80	0.2283	28	66	36	6	R4575.8
15/64	5.95	0.2343	28	66	36	6	R45715/64
	6.00	0.2362	28	66	36	6	R4576.0
	6.05	0.2382	34	79	36	8	R4576.05
	6.10	0.2402	34	79	36	8	R4576.1
	6.20	0.2441	34	79	36	8	R4576.2
	6.30	0.2480	34	79	36	8	R4576.3
1/4	6.35	0.2500	34	79	36	8	R4571/4
	6.40	0.2520	34	79	36	8	R4576.4

d ₁ Ø	d ₁ Ø	d ₁ decimal	l ₂	l ₁	l ₃	d ₂ Ø	e-Code
Inch	mm	Inch	mm	mm	mm	mm	
	6.50	0.2559	34	79	36	8	R4576.5
	6.60	0.2598	34	79	36	8	R4576.6
	6.70	0.2638	34	79	36	8	R4576.7
17/64	6.75	0.2657	34	79	36	8	R45717/64
	6.80	0.2677	34	79	36	8	R4576.8
	6.90	0.2717	34	79	36	8	R4576.9
	7.00	0.2756	34	79	36	8	R4577.0
	7.10	0.2795	41	79	36	8	R4577.1
9/32	7.14	0.2811	41	79	36	8	R4579/32
	7.30	0.2874	41	79	36	8	R4577.3
	7.40	0.2913	41	79	36	8	R4577.4
	7.50	0.2953	41	79	36	8	R4577.5
19/64	7.54	0.2969	41	79	36	8	R45719/64
	7.60	0.2992	41	79	36	8	R4577.6
	7.70	0.3031	41	79	36	8	R4577.7
	7.80	0.3071	41	79	36	8	R4577.8
	7.90	0.3110	41	79	36	8	R4577.9
5/16	7.94	0.3126	41	79	36	8	R4575/16
	8.00	0.3150	41	79	36	8	R4578.0
	8.05	0.3169	47	89	40	10	R4578.05
	8.10	0.3189	47	89	40	10	R4578.1
	8.20	0.3228	47	89	40	10	R4578.2
21/64	8.33	0.3280	47	89	40	10	R45721/64
	8.40	0.3307	47	89	40	10	R4578.4
	8.50	0.3346	47	89	40	10	R4578.5
	8.60	0.3386	47	89	40	10	R4578.6
	8.70	0.3425	47	89	40	10	R4578.7
11/32	8.73	0.3437	47	89	40	10	R45711/32
	8.80	0.3465	47	89	40	10	R4578.8
	8.90	0.3504	47	89	40	10	R4578.9
	9.00	0.3543	47	89	40	10	R4579.0
	9.10	0.3583	47	89	40	10	R4579.1
23/64	9.13	0.3594	47	89	40	10	R45723/64
	9.30	0.3661	47	89	40	10	R4579.3
	9.40	0.3701	47	89	40	10	R4579.4
	9.50	0.3740	47	89	40	10	R4579.5
3/8	9.52	0.3748	47	89	40	10	R4573/8
	9.60	0.3780	47	89	40	10	R4579.6
	9.70	0.3819	47	89	40	10	R4579.7
	9.80	0.3858	47	89	40	10	R4579.8
	9.90	0.3898	47	89	40	10	R4579.9
25/64	9.92	0.3906	47	89	40	10	R45725/64
	10.00	0.3937	47	89	40	10	R45710.0
	10.05	0.3957	55	102	45	12	R45710.05

R457



d ₁ Ø	d ₁ Ø	d ₁ decimal	l ₂	l ₁	l ₃	d ₂ Ø	e-Code	d ₁ Ø	d ₁ Ø	d ₁ decimal	l ₂	l ₁	l ₃	d ₂ Ø	e-Code
Inch	mm	Inch	mm	mm	mm	mm		Inch	mm	Inch	mm	mm	mm	mm	
	10.10	0.3976	55	102	45	12	R45710.1		14.00	0.5512	60	107	45	14	R45714.0
	10.20	0.4016	55	102	45	12	R45710.2		14.25	0.5610	65	115	48	16	R45714.25
	10.30	0.4055	55	102	45	12	R45710.3	9/16	14.29	0.5626	65	115	48	16	R4579/16
13/32	10.32	0.4063	55	102	45	12	R45713/32		14.50	0.5709	65	115	48	16	R45714.5
	10.40	0.4094	55	102	45	12	R45710.4	37/64	14.68	0.5780	65	115	48	16	R45737/64
	10.50	0.4134	55	102	45	12	R45710.5		14.80	0.5827	65	115	48	16	R45714.8
	10.60	0.4173	55	102	45	12	R45710.6		15.00	0.5906	65	115	48	16	R45715.0
27/64	10.72	0.4220	55	102	45	12	R45727/64	19/32	15.08	0.5937	65	115	48	16	R45719/32
	11.00	0.4331	55	102	45	12	R45711.0		15.10	0.5945	65	115	48	16	R45715.1
7/16	11.11	0.4374	55	102	45	12	R4577/16	39/64	15.48	0.6094	65	115	48	16	R45739/64
	11.20	0.4409	55	102	45	12	R45711.2		15.50	0.6102	65	115	48	16	R45715.5
	11.40	0.4488	55	102	45	12	R45711.4		15.80	0.6252	65	115	48	16	R45715.8
	11.50	0.4528	55	102	45	12	R45711.5	5/8	15.88	0.6252	65	115	48	16	R4575/8
29/64	11.51	0.4531	55	102	45	12	R45729/64		16.00	0.6299	65	115	48	16	R45716.0
	11.60	0.4567	55	102	45	12	R45711.6	41/64	16.27	0.6406	73	123	48	18	R45741/64
	11.80	0.4646	55	102	45	12	R45711.8		16.50	0.6496	73	123	48	18	R45716.5
15/32	11.91	0.4689	55	102	45	12	R45715/32	21/32	16.67	0.6563	73	123	48	18	R45721/32
	12.00	0.4724	55	102	45	12	R45712.0		17.00	0.6693	73	123	48	18	R45717.0
	12.05	0.4744	60	107	45	14	R45712.05	43/64	17.07	0.6720	73	123	48	18	R45743/64
	12.10	0.4764	60	107	45	14	R45712.1	11/16	17.46	0.6874	73	123	48	18	R45711/16
	12.20	0.4803	60	107	45	14	R45712.2		17.50	0.6890	73	123	48	18	R45717.5
31/64	12.30	0.4843	60	107	45	14	R45731/64	45/64	17.86	0.7031	73	123	48	18	R45745/64
	12.50	0.4921	60	107	45	14	R45712.5		18.00	0.7087	73	123	48	18	R45718.0
	12.70	0.5000	60	107	45	14	R45712.7	23/32	18.26	0.7189	79	131	50	20	R45723/32
1/2	12.70	0.5000	60	107	45	14	R4571/2		18.50	0.7283	79	131	50	20	R45718.5
	12.80	0.5039	60	107	45	14	R45712.8	47/64	18.65	0.7343	79	131	50	20	R45747/64
	13.00	0.5118	60	107	45	14	R45713.0		18.80	0.7480	79	131	50	20	R45718.8
33/64	13.10	0.5157	60	107	45	14	R45733/64		19.00	0.7480	79	131	50	20	R45719.0
17/32	13.49	0.5311	60	107	45	14	R45717/32	3/4	19.05	0.7500	79	131	50	20	R4573/4
	13.50	0.5315	60	107	45	14	R45713.5		19.50	0.7677	79	131	50	20	R45719.5
	13.80	0.5433	60	107	45	14	R45713.8		19.80	0.7874	79	131	50	20	R45719.8
35/64	13.89	0.5469	60	107	45	14	R45735/64		20.00	0.7874	79	131	50	20	R45720.0