








28	68.58±0.35	71.58±0.35
27	66.04±0.35	69.04±0.35
26	63.50±0.35	66.50±0.35
25	60.96±0.35	63.96±0.35
24	58.42±0.35	61.42±0.35
23	55.88±0.35	58.88±0.35
22	53.34±0.35	56.34±0.35
21	50.80±0.35	53.80±0.35
20	48.26±0.35	51.26±0.35
19	45.72±0.35	48.72±0.35
18	43.18±0.35	43.18±0.35
17	40.64±0.35	43.64±0.35
16	38.10±0.35	41.10±0.35
15	35.56±0.35	38.56±0.35
14	33.02±0.35	33.02±0.35
13	30.48±0.35	33.48±0.35
12	27.94±0.35	30.94±0.35
11	25.40±0.35	28.40±0.35
10	22.86±0.35	25.86±0.35
9	20.32±0.35	23.32±0.35
8	17.78±0.35	20.78±0.35
7	15.24±0.35	18.24±0.35
6	12.70±0.15	15.70±0.15
5	10.16±0.15	13.16±0.15
4	7.62±0.15	10.62±0.15
3	5.08±0.15	8.08±0.15
2	2.54±0.15	5.54±0.15
No. OF CCTS	DIM A	DIM B



C-C
PARTIAL SECTION



- NOTES:
1. MATERIAL: POLYAMIDE (PA66/6), UL94 V-0
COLOR: NATURAL PER THE FOLLOWING 89992-0086
 2. FOR USE WITH ANTI-FISH HOOKING TERMINAL No. 4809-#.
 3. SEE SHT. 3 FOR PARTS WITH VOIDS.
 4. OPTIONAL CENTRE PEGS TO BE USED ON Tcct & LARGER SIZES ONLY. SEE SHT. 3 FOR CHARTED ENG. No.'S.
 5. PART No. PRECEDED BY CODE LETTER DESIGNATES MFG. LOC'N. I=IRELAND

HOUSING STYLE

BLANK NO LOCKING RAMP

I = LOCKING RAMP & POL. RIB

S = OPT. PEG

R = LOCKING RAMP ONLY

No. OF CCTS

BLANK = STD. VOID

B = OPT. STYLE VOID

VOID CCT LOC'N.

6. 'MX#' MARK AND PART I.D. '6471' APPEAR EITHER ON FRONT OR BACK SIDE. SEE END VIEW FOR SIDE SIDE ORIENTATION.

ADJUST TOLERANCE		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: E2010-0105		DRAWN BY: 2009/09/23		mm		MM ONLY		1:1		METRIC		2.54 MM KK CRP TRM HSG IL	
CHKO: 2009/09/23		APPR: 2009/09/23		INCH		DRAWN BY: DATE		DATE		DATE		DATE	
4 PLACES ±---		3 PLACES ±---		2 PLACES ±0.15		1 PLACE ±0.25		ANGULAR ±---		APPROVED BY: DATE		DATE	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		SIZE		SEE CHART		DOCUMENT NO.		SHEET NO.		1 OF 5	
REV		DESCRIPTION		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SD-6471-N*-**							

PART NO

SEE CHART
DWG. NO.

~~SD-6471-N~~

7132-1283

10

9

8

7

6

5

4

3

2

1

F

E

D

C

B

A

PART No.	ENG No.	No. OF CIRCUITS	RAMP & POL. RIBS	DIM. A	DIM. B
22-01-2025	E-6471-021	2	YES	↑	↑
↑ -2035	↑ -031	3	↑		
-2045	-041	4			
-2055	-051	5			
-2065	-061	6			
-2075	-071	7			
-2085	-081	8			
-2095	-091	9			
-2105	-101	10			
-2115	-111	11			
-2125	-121	12			
-2135	-131	13			
-2145	-141	14			
-2155	-151	15			
-2165	-161	16			
-2175	-171	17			
-2185	-181	18			
-2195	-191	19			
-2205	-201	20			
-2215	-211	21			
-2225	-221	22			
↓ -2235	-231	23			
22-01-2245	-241	24			
NOT TOOLED	-251	25			
22-01-2265	-261	26			
NOT TOOLED	↓ -271	27	↓		
22-01-2285	E-6471-281	28	YES	↓	↓

PART No.	ENG No.	No. OF CIRCUITS	LOCKING FEATURE	DIM. A	DIM. B
22-01-2026	E-6471-2	2	NO	↑	↑
↑ -2036	↑ -3	3	↑		
-2046	-4	4			
-2056	-5	5			
-2066	-6	6			
-2076	-7	7			
-2086	-8	8			
-2096	-9	9			
-2106	-10	10			
-2116	-11	11			
-2126	-12	12			
-2136	-13	13			
-2146	-14	14			
-2156	-15	15			
-2166	-16	16			
-2176	-17	17			
-2186	-18	18			
-2196	-19	19			
-2206	-20	20			
↓ -2216	-21	21			
22-01-2226	-22	22			
NOT TOOLED	-23	23			
22-01-2246	-24	24			
NOT TOOLED	-25	25			
22-01-2266	-26	26			
22-01-2276	↓ -27	27	↓	↓	↓
22-01-2286	E-6471-28	28	NO	↓	↓

A	SEE SHEET 1.	REVISIONS	DIMENSIONS SHOWN (METRIC) INCH		DRWG BY	CADCAM FILENAME		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. & SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		
			UNLESS OTHERWISE SPECIFIED			SD-6471-N -				
			TOLERANCES: ANGULAR $\pm$			.502				
			INCH (METRIC)			.502				
L	TR	REV	3 PLACE $\pm$	$\pm$	CHK'D BY	SF	TITLE			
			2 PLACE $\pm$	$\pm$			2.54 mm KK Crp Trm Hsg Il			
			1 PLACE	$\pm$						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							
L	TR	REV	DESIGN DIMENSION ☐ (MM)	APP'D BY	SCALE	-	molex MOLEX EUROPE		SHEET NO.	DATE
			(PRIMARY) ☐ IN.				20F	15/07/00		
			EQUIVALENT DIMENSION ☐ (MM)							
			(SECONDARY) ☐ IN.							
							PART NO.	DWG NO.	SIZE	
							SEE CHART	SD-6471-N-...	B	

