

LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
G	14				P	REVISED PER 0L20-0020-97	06MAR97	MJS
					P1	REVISED PER ECO-09-021826	05JAN10	AEG

METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	 E13288 Listed
4 AWG SOLID OR STRANDED	4 AWG STRANDED

 LR7189 Certified	MILITARY P/N AND CLASS
4 AWG SOLID OR STRANDED	NOT APPLICABLE

- 1 STAMP AMP 4* APPROX AS SHOWN
- 2 TIN PLATE 0.00254[.000100] MIN THK
PER MIL-T-10727
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER
D.RENAUD/D.SINISI

OBSOLETE	2	25	LOOSE PIECE, BAG	8-33471-5
	2	50	LOOSE PIECE, BOX	8-33471-2
OBSOLETE	2	500	LOOSE PIECE, BOX	2-33471-3
3 OBSOLETE	2	500	ON TAPE, REEL	1-33471-2
OBSOLETE	CLEANED	-	LOOSE PIECE	1-33471-1
	2	-	LOOSE PIECE	33471

AMP INCORPORATED

CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:

170° C MAX

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

VOLTAGE RATING:

NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:

16.8-26.7mm²[33,100-52,600] CIR MILS
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED

DIMENSIONS IN mm [INCHES]
TOLERANCES ON :

2 PLC DEC ± -
3 PLC DEC ± -
ANGLES ± -

MATERIAL

COPPER PER
ASTM B-152
ANNEALED

FINISH

SEE TABLE

DR 3-29-93
TA BRINKMAN

CHK 3-29-93
DA PATTERSON

APPD 3-29-93
DE MILLER

APPD 3-29-93
JL MECKLEY

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-



AMP Incorporated

Harrisburg, PA 17105-3608

NAME

TERMINAL, RING TONGUE,
SOLISTRAND™

SIZE

C 00779

DRAWING NO

C- 33471

SCALE

4:1

SHEET

10F 1