

Inline terminal - IB IL AI/TEMP 4 RTD-XC-PAC - 2701165

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Inline analog input terminal, version for extreme conditions, complete with accessories (connector plug and marking field), 4 inputs, 0 - 10 V, resistance temperature detector (RTD), 2-conductor connection technology

Product description


The terminal block has been developed for use in an Inline station. The terminal has four inputs that may be configured independently of each other and either for measuring voltages or resistances or for RTDs.

The sensors are connected using the 2-wire connection method, so that a nominal resistance of at least 1000W is recommended when sensors with a relatively small temperature coefficient (e.g., platinum sensors) are used. The resistance measurement with conversion into temperature values can be used for the temperature measurement with NTC resistors. The advantage of these resistors is a large temperature coefficient.

Why buy this product

- Voltage inputs 0 V ... 10 V
- Inputs for temperature measurements
- Connection of sensors in 2-wire technology
- Diagnostic and status indicators
- Can be used under extreme ambient conditions
- Extended temperature range of -40°C ... +70°C (see "Tested successfully: use under extreme ambient conditions" in the data sheet)
- Coated PCBs

Key commercial data

Packing unit	1 pc
GTIN	 4 046356 716895
Weight per Piece (excluding packing)	68.0 g
Custom tariff number	85389091
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	12.2 mm
Height	140.5 mm

Inline terminal - IB IL AI/TEMP 4 RTD-XC-PAC - 2701165

Technical data

Dimensions

Depth	71.5 mm
-------	---------

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
	-40 °C ... 70 °C (See "Tested successfully: use under extreme ambient conditions" in the data sheet.)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Degree of protection	IP20

General

Weight	68 g
Note on weight specifications	with connector
Mounting type	DIN rail
Protection class	III, IEC 61140, EN 61140, VDE 0140-1

Interfaces

Fieldbus system	Lokalbus
Designation	Inline local bus
Connection method	Inline data jumper
Transmission speed	500 kBit/s
Transmission physics	Copper

Classifications

eCl@ss

eCl@ss 4.0	27240405
eCl@ss 4.1	27240405
eCl@ss 5.0	27242201
eCl@ss 5.1	27242602
eCl@ss 6.0	27242602
eCl@ss 7.0	27242602
eCl@ss 8.0	27242601

ETIM

ETIM 3.0	EC001599
ETIM 4.0	EC001599
ETIM 5.0	EC001596

Inline terminal - IB IL AI/TEMP 4 RTD-XC-PAC - 2701165

Classifications

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404