

THIS DRAWING IS UNPUBLISHED.





RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

REVISIONS

P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
		DG2		REVISED PER ECO-11-005140	01APR11	HMR



1 - DIM'S. IN BRACKETS ARE IN INCHES.

2 - CONTINUOUS STRIP ON REELS.

3 - FOREIGN PRODUCTION ONLY

4 - PAPER INTERLAY BETWEEN LAYERS

5 - OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

FINISH	MATERIAL	INSULATION RANGE	WIRE SIZE	PART NO
OBSOLETE 3/4	TIN	[.0150] 0.38 BRASS	[.120-.160] 3.05-4.06	18-14 0.8-2mm ² 42098-8
5 OBSOLETE	TIN	[.0150] 0.38 PHOS. BRZ.	[.120-.160] 3.05-4.06	18-14 0.8-2mm ² 42098-7
5 OBSOLETE	PRE-TIN	[.0150] 0.38 BRASS	[.120-.160] 3.05-4.06	18-14 0.8-2mm ² 42098-6
OBSOLETE 3/4	NONE	[.0150] 0.38 PHOS. BRZ.	[.120-.160] 3.05-4.06	18-14 0.8-2mm ² 42098-5
OBSOLETE	NICKEL	[.015] 0.38 PHOS. BRZ.	[.120-.160] 3.05-4.06	18-14 0.8-2mm ² 42098-4
3 SILVER	[.0150] 0.38 BRASS	[.120-.160] 3.05-4.06	18-14 0.8-2mm ²	42098-3
3 PRE-TIN	[.0150] 0.38 BRASS	[.120-.160] 3.05-4.06	18-14 0.8-2mm ²	42098-2
3 NONE	[.0150] 0.38 BRASS	[.120-.160] 3.05-4.06	18-14 0.8-2mm ²	42098-1

METRIC

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS [±.015] 0.38 ANGLES

MATERIAL

FINISH

CONTRACT NO

DR

CHK

APPR

APRD

DSGN APPD

OTHER APPD

STE

TE Connectivity

NAME

250 SERIES FASTIN-FASTON TAB

SIZE

B

FSCM NO

00779

DRAWING NO

42098

SCALE

#

SHEET

CUSTOMER DRAWING