

Wiha SoftFinish® ESD.

For use on electrostatically sensitive components.

For TORX® screws. Bit holder.



362ESD SoftFinish® ESD TORX® screwdriver.
Dissipative handle, ESD-safe.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection. Surface resistance $10^6 - 10^9$ Ohm.

Standards: IEC 61340-5-1.

Application: For working on electrostatically sensitive components.

Order-No.	⊛	⊖	⊙	⊕	⊕	⊕
31432 3	T3	60	2.5	164	23	10
27148 0	T4	60	2.5	164	23	10
27641 6	T5	60	3.5	164	23	10
27149 7	T6	60	3.5	164	23	10
31901 4	T7	60	3.5	164	23	10
22436 3	T8	60	3.5	164	23	10
27145 9	T9	60	4.0	171	30	10
27144 2	T10	80	4.0	191	30	10
27146 6	T15	80	4.0	191	30	10
27147 3	T20	100	4.0	218	36	10



387ESD ESD bit holder with handle, quick release holder, 1/4".
Dissipative handle, ESD-safe.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection. Surface resistance $10^6 - 10^9$ Ohm.

Standards: Handle: IEC 61340-5-1.

Output: DIN 3126, ISO 1173, style D 6,3, F 6,3, double bits.

Input: DIN 3126, ISO 1173, style E 6,3.

Bit holder: Stainless steel with retaining ring.

Application: For working on electrostatically sensitive components.

With integrated CentroFix bit holder, suitable for all bits and bit drills with the style C 6,3, E 6,3 or double bits.

Extra: True single-handed operation, extremely high retention force of bits (up to 20 kg) and virtually no play between bit and holder thanks to special closing and holding mechanism.

Order-No.	⊙	⊖	⊕	⊕	⊕
32161 1	1/4	38	148	30	10

Safety Notice:

Wiha ESD screwdrivers are non-insulated, therefore not suitable for working on live parts.

Sets.



302ESD HK5 01 SoftFinish® ESD slotted/ Phillips screwdriver set, 5 pcs.
Dissipative handle, ESD-safe.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection. Surface resistance $10^6 - 10^9$ Ohm.

Standards: IEC 61340-5-1.

Application: For working on electrostatically sensitive components.

Order-No.	Series				⊖
27252 4	302ESD HK5 01				1
⊙	302ESD	3.0x100	4.0x100		
⊕	311ESD	PH0x60	PH1x80	PH2x100	



362ESD K5 SoftFinish® ESD TORX® screwdriver set, 5 pcs.
Dissipative handle, ESD-safe.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection. Surface resistance $10^6 - 10^9$ Ohm.

Standards: IEC 61340-5-1.

Application: For working on electrostatically sensitive components.

Order-No.	Series				⊖
27253 1	362ESD K5				1
⊛	362ESD	T6x60	T8x60	T9x60	
		T10x80	T15x80		