



LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			D2	REVISED PER ECO-11-004917	11MAR11	RK HMR



- 1 FOR 1.02[.040] TO 2.54[.100] WIRE INSULATION DIA
- 2 TONGUE MATERIAL THK 0.58±0.05[.023±.002]
- 3 APPLIES FROM EDGE OF METAL BARREL TO CENTERLINE OF STUD HOLE.

1	323989 ON TAPE	BODY&SLEEVE: COPPER ASTM-B152 TIN PL ASTM-B545 INSULATION: NATURAL NYLON ASTM-D4066 TYPE I	1-323989-0
1	WIRE TERMINAL		323989
QTY	DESCRIPTION	MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 19MAR10	TE Connectivity					
		CHK JEFF RUTH 19MAR10						
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD TOM MICHIELUTTI 19MAR10	NAME TERMINAL, NYLON – PIDG – RING TONGUE WIRE SIZE: 24–20					
	0 PLC ± –	PRODUCT SPEC	SIZE A3			CAGE CODE 00779	DRAWING NO C-323989	RESTRICTED TO —
	1 PLC ± –	—						
	2 PLC ± –	APPLICATION SPEC						
	3 PLC ± 0.20 [.008]	—						
	4 PLC ± –	—						
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT —						
CUSTOMER DRAWING			SCALE 10:1		SHEET 1 OF 1		REV D2	