


## Cam followers



Dimensions				Basic load ratings		Fatigue load limit	Maximum radial loads		Limiting speed	Mass	Designation
D	d	B	C	dynamic C	static C <sub>0</sub>	P <sub>u</sub>	dynamic F <sub>r</sub>	static F <sub>0r</sub>	r/min	kg	-
mm				kN	kN	kN	kN				
72	24	80	29	26	48	6	100	143	2400	1,05	KR 72 PPA



**Appertaining grease nipple(s)**

NIP A3x9.5

**Appertaining hexagonal nut**

Size, mm

M 24x1.5

Rec. tightening torque, Nm

220

**Internal hexagon in stud**

Key width, mm

14