



ENGLISH

## Product Datasheet

# 100mm Braked Swivel Castor with Grey Rubber Tyred Wheel, 70kg load capacity



Specification	
Application	General Purpose / Industrial
Features	Ball Bearing Swivel Head
Fixing Centres	80x60mm
Fixing Centres Length	80mm
Fixing Centres Width	60mm
Fixing Hole Size	8mm
Fixing Plate Dimensions	102x84mm
Fixing Plate Length	102mm
Fixing Plate Width	84mm
Hub Bearing Type	Roller
Hub Material	Polypropylene
Load Capacity	70kg
Number of Fixing Holes	4
Overall Height	128mm
Rotation	Swivel & Brake
Tyre Material	Grey Rubber Tyre
Weight Class	Light Duty
Wheel Diameter	100mm
Wheel Width	24mm